

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843520

Luminaire Tested: **LD4C25DE010B2750 EU4C25B35 4LBCSMB**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843520
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25DE010B2750 EU4C25B35 4LBCSMB
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1740.9 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843520

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P843520

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87337
5°	87300
10°	87249
15°	86411
20°	85803
25°	84938
30°	83512
35°	82112
40°	79690
45°	76985
50°	72399
55°	65520
60°	57569
65°	48459
70°	37860
75°	26487
80°	14999
85°	10290



TEST NUMBER: P843520

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	3.9
10°-20°	191.8	11.0
20°-30°	288.5	16.6
30°-40°	341.9	19.6
40°-50°	340.3	19.5
50°-60°	274.3	15.8
60°-70°	165.9	9.5
70°-80°	61.6	3.5
80°-90°	9.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	547.7	31.5
0°-40°	889.6	51.1
0°-60°	1504.2	86.4
0°-90°	1740.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1740.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	711	
5°	708	67
15°	679	192
25°	627	289
35°	548	342
45°	443	340
55°	306	274
65°	167	166
75°	56	62
85°	7	9
90°	0	



TEST NUMBER: P843520

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	710.9
2.5°	710.9
5°	707.9
7.5°	705.8
10°	699.4
12.5°	688.8
15°	679.4
17.5°	669.0
20°	656.3
22.5°	643.6
25°	626.6
27.5°	608.7
30°	588.7
32.5°	569.6
35°	547.5
37.5°	524.4
40°	496.9
42.5°	470.5
45°	443.1
47.5°	412.4
50°	378.8
52.5°	343.8
55°	305.9
57.5°	272.2
60°	234.3
62.5°	200.4
65°	166.7
67.5°	135.0
70°	105.4
72.5°	79.1
75°	55.8
77.5°	35.9
80°	21.2
82.5°	12.7
85°	7.3
87.5°	3.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)