

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843528

Luminaire Tested: **LD4C25DE010B2750 EU4C25B35 4LBNH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25DE010B2750 EU4C25B35 4LBNH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1573.8 lumens
Efficiency: N/A
Efficacy: 52.8 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843528

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P843528

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	242746
5°	237347
10°	219458
15°	196924
20°	173332
25°	149177
30°	120126
35°	79982
40°	41601
45°	18834
50°	8161
55°	5483
60°	3514
65°	2500
70°	2047
75°	1377
80°	0
85°	0



TEST NUMBER: P843528

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.3	11.3
10°-20°	432.4	27.5
20°-30°	502.1	31.9
30°-40°	332.5	21.1
40°-50°	93.3	5.9
50°-60°	23.4	1.5
60°-70°	8.8	0.6
70°-80°	3.0	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1112.8	70.7
0°-40°	1445.3	91.8
0°-60°	1562.0	99.2
0°-90°	1573.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1573.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1976	
5°	1925	178
15°	1548	432
25°	1100	502
35°	533	332
45°	108	93
55°	26	23
65°	9	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P843528

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1975.9
2.5°	1967.3
5°	1924.6
7.5°	1850.3
10°	1759.2
12.5°	1656.5
15°	1548.3
17.5°	1442.7
20°	1325.8
22.5°	1217.4
25°	1100.5
27.5°	989.4
30°	846.8
32.5°	695.7
35°	533.3
37.5°	382.1
40°	259.4
42.5°	168.2
45°	108.4
47.5°	65.7
50°	42.7
52.5°	31.3
55°	25.6
57.5°	20.0
60°	14.3
62.5°	11.4
65°	8.6
67.5°	5.7
70°	5.7
72.5°	2.9
75°	2.9
77.5°	2.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)