

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843536

Luminaire Tested: **LD4C25DE010B2750 EU4C25B40 4LBCSMW**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843536
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25DE010B2750 EU4C25B40 4LBSCMW
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2156.5 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843536

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBCSMW

Luminous Intensity Polar Plot





TEST NUMBER: P843536

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBSCMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108197
5°	108142
10°	108082
15°	107054
20°	106277
25°	105230
30°	103444
35°	101729
40°	98710
45°	95366
50°	89695
55°	81135
60°	71280
65°	60029
70°	46911
75°	32847
80°	18465
85°	12827



TEST NUMBER: P843536

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBCSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.4	3.9
10°-20°	237.6	11.0
20°-30°	357.4	16.6
30°-40°	423.6	19.6
40°-50°	421.5	19.5
50°-60°	339.8	15.8
60°-70°	205.5	9.5
70°-80°	76.3	3.5
80°-90°	11.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	678.5	31.5
0°-40°	1102.0	51.1
0°-60°	1863.4	86.4
0°-90°	2156.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2156.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	881	
5°	877	83
15°	842	238
25°	776	357
35°	678	424
45°	549	422
55°	379	340
65°	206	206
75°	69	76
85°	9	11
90°	0	



TEST NUMBER: P843536

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBCSMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	880.7
2.5°	880.7
5°	876.9
7.5°	874.2
10°	866.4
12.5°	853.4
15°	841.7
17.5°	828.7
20°	812.9
22.5°	797.2
25°	776.3
27.5°	754.0
30°	729.2
32.5°	705.7
35°	678.3
37.5°	649.5
40°	615.5
42.5°	583.0
45°	548.9
47.5°	510.9
50°	469.3
52.5°	426.0
55°	378.8
57.5°	337.3
60°	290.1
62.5°	248.3
65°	206.5
67.5°	167.2
70°	130.6
72.5°	98.0
75°	69.2
77.5°	44.4
80°	26.1
82.5°	15.7
85°	9.1
87.5°	3.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)