

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843247

Luminaire Tested: **LD4C08DE010B2750 EU4C08B35 4LBMLI**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08DE010B2750 EU4C08B35 4LBMLI
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 772.2 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843247

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B35 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P843247

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B35 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149525
5°	146976
10°	135053
15°	113108
20°	90614
25°	72806
30°	54190
35°	30970
40°	14530
45°	6168
50°	1969
55°	1007
60°	713
65°	552
70°	359
75°	0
80°	0
85°	0



TEST NUMBER: P843247

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B35 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.2	14.3
10°-20°	246.4	31.9
20°-30°	245.0	31.7
30°-40°	133.4	17.3
40°-50°	30.8	4.0
50°-60°	4.4	0.6
60°-70°	1.7	0.2
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	601.5	77.9
0°-40°	734.9	95.2
0°-60°	770.1	99.7
0°-90°	772.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	772.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1217	
5°	1192	110
15°	889	246
25°	537	245
35°	206	133
45°	36	31
55°	5	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P843247

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B35 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1217.1
2.5°	1214.3
5°	1191.8
7.5°	1146.2
10°	1082.6
12.5°	989.2
15°	889.3
17.5°	790.3
20°	693.1
22.5°	613.7
25°	537.1
27.5°	464.3
30°	382.0
32.5°	290.5
35°	206.5
37.5°	139.2
40°	90.6
42.5°	57.0
45°	35.5
47.5°	20.5
50°	10.3
52.5°	5.6
55°	4.7
57.5°	2.9
60°	2.9
62.5°	1.9
65°	1.9
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)