

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843254

Luminaire Tested: **LD4C08DE010B2750 EU4C08B40 4LBCSMB**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843254
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08DE010B2750 EU4C08B40 4LBCSMB
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 563.7 lumens
Efficiency: N/A
Efficacy: 58.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843254

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B40 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P843254

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B40 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87																			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74																			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63																			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55																			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48																			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33																			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30																			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28281
5°	28266
10°	28243
15°	27981
20°	27782
25°	27517
30°	27038
35°	26591
40°	25804
45°	24932
50°	23451
55°	21205
60°	18625
65°	15669
70°	12285
75°	8592
80°	4882
85°	3242



TEST NUMBER: P843254

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B40 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.8	3.9
10°-20°	62.1	11.0
20°-30°	93.4	16.6
30°-40°	110.7	19.6
40°-50°	110.2	19.6
50°-60°	88.8	15.8
60°-70°	53.7	9.5
70°-80°	20.0	3.5
80°-90°	3.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.3	31.5
0°-40°	288.1	51.1
0°-60°	487.1	86.4
0°-90°	563.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	563.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	230	
5°	229	22
15°	220	62
25°	203	93
35°	177	111
45°	144	110
55°	99	89
65°	54	54
75°	18	20
85°	2	3
90°	0	



TEST NUMBER: P843254

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B40 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	230.2
2.5°	230.2
5°	229.2
7.5°	228.6
10°	226.4
12.5°	223.1
15°	220.0
17.5°	216.6
20°	212.5
22.5°	208.4
25°	203.0
27.5°	197.0
30°	190.6
32.5°	184.5
35°	177.3
37.5°	169.8
40°	160.9
42.5°	152.4
45°	143.5
47.5°	133.6
50°	122.7
52.5°	111.4
55°	99.0
57.5°	88.2
60°	75.8
62.5°	64.9
65°	53.9
67.5°	43.7
70°	34.2
72.5°	25.6
75°	18.1
77.5°	11.6
80°	6.9
82.5°	4.1
85°	2.3
87.5°	1.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)