

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843332

Luminaire Tested: **LD4C10DE010B40 EU4C10B40 4LBNH**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P843332  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C10DE010B40 EU4C10B40 4LBNH  
Description: 4in Downlight with BioUp LEDs  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 726.5 lumens  
Efficiency: N/A  
Efficacy: 54.6 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843332

CATALOG NUMBER: LD4C10DE010B40 EU4C10B40 4LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P843332

CATALOG NUMBER: LD4C10DE010B40 EU4C10B40 4LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	112079
5°	109572
10°	101321
15°	90926
20°	80038
25°	68875
30°	55467
35°	36924
40°	19197
45°	8687
50°	3784
55°	2527
60°	1622
65°	1134
70°	934
75°	617
80°	0
85°	0



TEST NUMBER: P843332

CATALOG NUMBER: LD4C10DE010B40 EU4C10B40 4LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.3	11.3
10°-20°	199.7	27.5
20°-30°	231.8	31.9
30°-40°	153.5	21.1
40°-50°	43.0	5.9
50°-60°	10.8	1.5
60°-70°	4.0	0.6
70°-80°	1.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	513.8	70.7
0°-40°	667.3	91.8
0°-60°	721.1	99.3
0°-90°	726.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	726.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	912	
5°	888	82
15°	715	200
25°	508	232
35°	246	154
45°	50	43
55°	12	11
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P843332

CATALOG NUMBER: LD4C10DE010B40 EU4C10B40 4LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	912.3
2.5°	908.3
5°	888.5
7.5°	854.4
10°	812.2
12.5°	764.8
15°	714.9
17.5°	666.1
20°	612.2
22.5°	562.1
25°	508.1
27.5°	456.8
30°	391.0
32.5°	321.2
35°	246.2
37.5°	176.4
40°	119.7
42.5°	77.6
45°	50.0
47.5°	30.2
50°	19.8
52.5°	14.5
55°	11.8
57.5°	9.2
60°	6.6
62.5°	5.3
65°	3.9
67.5°	2.6
70°	2.6
72.5°	1.3
75°	1.3
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)