

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430866

Luminaire Tested: **LAM4B412R609727DE01021MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430866
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B412R609727DE01021MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4730.6 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430866

CATALOG NUMBER: LAM4B412R609727DE01021MW

Luminous Intensity Polar Plot





TEST NUMBER: P430866

CATALOG NUMBER: LAM4B412R609727DE01021MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67	67	67	67
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2682406
5°	2592460
10°	2568279
15°	2504579
20°	2311399
25°	2069912
30°	1601727
35°	959532
40°	368661
45°	134734
50°	5296
55°	3957
60°	4539
65°	2685
70°	3318
75°	4384
80°	6535
85°	0



TEST NUMBER: P430866

CATALOG NUMBER: LAM4B412R609727DE01021MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	497.1	10.5
10°-20°	1364.1	28.8
20°-30°	1701.7	36.0
30°-40°	991.4	21.0
40°-50°	165.5	3.5
50°-60°	4.4	0.1
60°-70°	3.1	0.1
70°-80°	2.4	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3562.9	75.3
0°-40°	4554.3	96.3
0°-60°	4724.1	99.9
0°-90°	4730.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4730.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5437	
5°	5234	497
15°	4903	1364
25°	3802	1702
35°	1593	991
45°	193	165
55°	5	4
65°	2	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P430866

CATALOG NUMBER: LAM4B412R609727DE01021MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5436.8
2.5°	5347.1
5°	5234.5
7.5°	5170.1
10°	5126.4
12.5°	5055.2
15°	4903.4
17.5°	4675.9
20°	4402.3
22.5°	4124.1
25°	3802.3
27.5°	3356.3
30°	2811.5
32.5°	2202.3
35°	1593.1
37.5°	1004.6
40°	572.4
42.5°	335.6
45°	193.1
47.5°	66.7
50°	6.9
52.5°	4.6
55°	4.6
57.5°	4.6
60°	4.6
62.5°	4.6
65°	2.3
67.5°	2.3
70°	2.3
72.5°	2.3
75°	2.3
77.5°	2.3
80°	2.3
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)