

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P430867

Luminaire Tested: **LAM4B412R609730DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P430867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B412R609730DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4982.3 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 54.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P430867
CATALOG NUMBER: LAM4B412R609730DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P430867

CATALOG NUMBER: LAM4B412R609730DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67	67	67	67
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2825141
5°	2730441
10°	2704999
15°	2637893
20°	2434417
25°	2180095
30°	1686955
35°	1010608
40°	388305
45°	141921
50°	5603
55°	4129
60°	4736
65°	2802
70°	3462
75°	4575
80°	6819
85°	0



TEST NUMBER: P430867

CATALOG NUMBER: LAM4B412R609730DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	523.5	10.5
10°-20°	1436.7	28.8
20°-30°	1792.3	36.0
30°-40°	1044.1	21.0
40°-50°	174.3	3.5
50°-60°	4.6	0.1
60°-70°	3.3	0.1
70°-80°	2.5	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3752.5	75.3
0°-40°	4796.7	96.3
0°-60°	4975.5	99.9
0°-90°	4982.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4982.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5726	
5°	5513	524
15°	5164	1437
25°	4005	1792
35°	1678	1044
45°	203	174
55°	5	5
65°	2	3
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P430867

CATALOG NUMBER: LAM4B412R609730DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	5726.1
2.5°	5631.7
5°	5513.1
7.5°	5445.3
10°	5399.3
12.5°	5324.2
15°	5164.4
17.5°	4924.7
20°	4636.6
22.5°	4343.6
25°	4004.7
27.5°	3535.0
30°	2961.1
32.5°	2319.5
35°	1677.9
37.5°	1058.1
40°	602.9
42.5°	353.5
45°	203.4
47.5°	70.2
50°	7.3
52.5°	4.8
55°	4.8
57.5°	4.8
60°	4.8
62.5°	4.8
65°	2.4
67.5°	2.4
70°	2.4
72.5°	2.4
75°	2.4
77.5°	2.4
80°	2.4
82.5°	2.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)