

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843388

Luminaire Tested: **LD4C15DE010B35 EU4C15B35 4LBNH**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P843388  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C15DE010B35 EU4C15B35 4LBNH  
Description: 4in Downlight with BioUp LEDs  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 948.8 lumens  
Efficiency: N/A  
Efficacy: 55.8 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 17  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843388

CATALOG NUMBER: LD4C15DE010B35 EU4C15B35 4LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P843388

CATALOG NUMBER: LD4C15DE010B35 EU4C15B35 4LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	76	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	146331
5°	143079
10°	132296
15°	118704
20°	104499
25°	89940
30°	72419
35°	48202
40°	25082
45°	11363
50°	4931
55°	3299
60°	2113
65°	1512
70°	1257
75°	807
80°	0
85°	0



TEST NUMBER: P843388

CATALOG NUMBER: LD4C15DE010B35 EU4C15B35 4LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	107.5	11.3
10°-20°	260.7	27.5
20°-30°	302.7	31.9
30°-40°	200.4	21.1
40°-50°	56.2	5.9
50°-60°	14.1	1.5
60°-70°	5.3	0.6
70°-80°	1.8	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.8	70.7
0°-40°	871.3	91.8
0°-60°	941.6	99.2
0°-90°	948.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	948.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1191	
5°	1160	107
15°	933	261
25°	664	303
35°	321	200
45°	65	56
55°	15	14
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P843388

CATALOG NUMBER: LD4C15DE010B35 EU4C15B35 4LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1191.1
2.5°	1185.9
5°	1160.2
7.5°	1115.5
10°	1060.5
12.5°	998.5
15°	933.3
17.5°	869.7
20°	799.3
22.5°	733.9
25°	663.5
27.5°	596.4
30°	510.5
32.5°	419.4
35°	321.4
37.5°	230.4
40°	156.4
42.5°	101.4
45°	65.4
47.5°	39.6
50°	25.8
52.5°	18.9
55°	15.4
57.5°	12.1
60°	8.6
62.5°	6.9
65°	5.2
67.5°	3.5
70°	3.5
72.5°	1.7
75°	1.7
77.5°	1.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)