

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274265

Luminaire Tested: **LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274265
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35290)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0LI
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, MEDIUM DISTRIBUTION WITH SPECULAR FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1013.4 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274265

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P274265

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174544
5°	171580
10°	157644
15°	132028
20°	105773
25°	84992
30°	63258
35°	36133
40°	16959
45°	7201
50°	2295
55°	1162
60°	809
65°	646
70°	383
75°	0
80°	0
85°	0



TEST NUMBER: P274265

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.6	14.3
10°-20°	323.4	31.9
20°-30°	321.5	31.7
30°-40°	175.1	17.3
40°-50°	40.5	4.0
50°-60°	5.7	0.6
60°-70°	2.1	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	789.5	77.9
0°-40°	964.6	95.2
0°-60°	1010.8	99.7
0°-90°	1013.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1013.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1598	
5°	1564	145
15°	1167	323
25°	705	321
35°	271	175
45°	47	40
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P274265

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1597.5
2.5°	1593.8
5°	1564.4
7.5°	1504.3
10°	1420.9
12.5°	1298.3
15°	1167.2
17.5°	1037.2
20°	909.7
22.5°	805.5
25°	705.0
27.5°	609.3
30°	501.4
32.5°	381.3
35°	270.9
37.5°	182.7
40°	118.9
42.5°	74.8
45°	46.6
47.5°	27.0
50°	13.5
52.5°	7.4
55°	6.1
57.5°	3.7
60°	3.7
62.5°	2.5
65°	2.5
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)