

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843534

Luminaire Tested: **LD4C25DE010B40 EU4C25B40 4LBCSMB**

Issue Date: 5/7/2024

Test Information

Test Method: LM-79-08
Report Number: P843534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25DE010B40 EU4C25B40 4LBCSMB
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1726.0 lumens
Efficiency: N/A
Efficacy: 57.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843534

CATALOG NUMBER: LD4C25DE010B40 EU4C25B40 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P843534

CATALOG NUMBER: LD4C25DE010B40 EU4C25B40 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86599
5°	86548
10°	86513
15°	85686
20°	85071
25°	84233
30°	82803
35°	81422
40°	79000
45°	76324
50°	71787
55°	64942
60°	57078
65°	48023
70°	37536
75°	26297
80°	14786
85°	10290



TEST NUMBER: P843534

CATALOG NUMBER: LD4C25DE010B40 EU4C25B40 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.8	3.9
10°-20°	190.2	11.0
20°-30°	286.1	16.6
30°-40°	339.0	19.6
40°-50°	337.4	19.5
50°-60°	272.0	15.8
60°-70°	164.5	9.5
70°-80°	61.1	3.5
80°-90°	9.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	543.0	31.5
0°-40°	882.0	51.1
0°-60°	1491.4	86.4
0°-90°	1726.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1726.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	705	
5°	702	67
15°	674	190
25°	621	286
35°	543	339
45°	439	337
55°	303	272
65°	165	164
75°	55	61
85°	7	9
90°	0	



TEST NUMBER: P843534

CATALOG NUMBER: LD4C25DE010B40 EU4C25B40 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	704.9
2.5°	704.9
5°	701.8
7.5°	699.7
10°	693.5
12.5°	683.0
15°	673.7
17.5°	663.2
20°	650.7
22.5°	638.1
25°	621.4
27.5°	603.5
30°	583.7
32.5°	564.8
35°	542.9
37.5°	519.8
40°	492.6
42.5°	466.5
45°	439.3
47.5°	408.9
50°	375.6
52.5°	341.0
55°	303.2
57.5°	269.9
60°	232.3
62.5°	198.7
65°	165.2
67.5°	133.8
70°	104.5
72.5°	78.5
75°	55.4
77.5°	35.6
80°	20.9
82.5°	12.6
85°	7.3
87.5°	3.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)