

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777678

Luminaire Tested: LERS4D08D010-EC4DR300210IC9024-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P777678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D08D010-EC4DR300210IC9024-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 703.9 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P777678

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9024-4LBS1LI

Luminous Intensity Polar Plot



TEST NUMBER: P777678

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9024-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	173248	173248	173248
5°	168270	168078	168286
10°	145748	144722	145717
15°	95092	94585	94110
20°	47285	49061	47220
25°	23825	26857	23335
30°	9537	10394	8308
35°	4420	4233	3551
40°	1908	2118	1799
45°	1342	1678	1353
50°	464	1215	488
55°	267	507	280
60°	184	214	184
65°	127	127	127
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 1678 cd/sqm



TEST NUMBER: P777678

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9024-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.0	28.3
10°-20°	320.5	45.5
20°-30°	138.5	19.7
30°-40°	31.6	4.5
40°-50°	10.8	1.5
50°-60°	2.6	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	658.1	93.5
0°-40°	689.7	98.0
0°-60°	703.1	99.9
0°-90°	703.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	703.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2263	2263	2263	2263	2263	
5°	2190	2188	2188	2192	2190	199
15°	1200	1186	1194	1190	1188	321
25°	282	293	318	285	276	135
35°	47	48	45	45	38	32
45°	12	16	16	16	12	9
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P777678

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9024-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2263.4	2263.4	2263.4	2263.4	2263.4
2.5°	2248.4	2246.8	2247.7	2248.8	2249.3
5°	2190.0	2187.9	2187.5	2192.1	2190.2
7.5°	2072.4	2069.4	2064.8	2075.2	2084.8
10°	1875.2	1871.9	1862.0	1866.9	1874.8
12.5°	1584.2	1573.4	1573.2	1588.7	1586.6
15°	1200.0	1185.6	1193.6	1189.7	1187.6
17.5°	807.0	801.4	812.1	808.9	795.0
20°	580.5	581.9	602.3	592.1	579.7
22.5°	423.6	428.9	452.9	426.6	416.9
25°	282.1	292.7	318.0	285.3	276.3
27.5°	173.5	178.4	204.0	171.3	166.3
30°	107.9	105.5	117.6	100.9	94.0
32.5°	70.8	67.7	71.6	64.2	58.7
35°	47.3	48.4	45.3	45.0	38.0
37.5°	29.6	34.0	30.0	32.0	24.5
40°	19.1	24.7	21.2	23.4	18.0
42.5°	15.6	19.0	17.5	18.6	16.0
45°	12.4	15.5	15.5	15.5	12.5
47.5°	6.9	10.3	13.2	10.5	7.3
50°	3.9	5.2	10.2	5.4	4.1
52.5°	2.7	3.0	7.0	3.1	2.8
55°	2.0	2.1	3.8	2.2	2.1
57.5°	1.5	1.7	2.0	1.7	1.5
60°	1.2	1.2	1.4	1.3	1.2
62.5°	0.9	0.9	1.0	0.9	0.9
65°	0.7	0.7	0.7	0.7	0.7
67.5°	0.3	0.5	0.5	0.5	0.5
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)