

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777689

Luminaire Tested: LERS4D08D010-EC4DR300210IC9035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P777689
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D08D010-EC4DR300210IC9035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 811.1 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P777689

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9035-4LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P777689

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	199656	199656	199656
5°	193918	193695	193934
10°	167970	166781	167923
15°	109586	109000	108453
20°	54494	56538	54421
25°	27448	30953	26891
30°	10986	11976	9572
35°	5093	4887	4093
40°	2198	2448	2068
45°	1548	1927	1570
50°	536	1405	572
55°	307	587	320
60°	214	260	214
65°	127	127	127
70°	90	45	90
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 1927 cd/sqm



TEST NUMBER: P777689

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.4	28.3
10°-20°	369.4	45.5
20°-30°	159.6	19.7
30°-40°	36.4	4.5
40°-50°	12.5	1.5
50°-60°	3.1	0.4
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	758.4	93.5
0°-40°	794.8	98.0
0°-60°	810.3	99.9
0°-90°	811.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	811.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2608	2608	2608	2608	2608	
5°	2524	2521	2521	2526	2524	230
15°	1383	1366	1376	1371	1369	370
25°	325	337	366	329	318	156
35°	54	56	52	52	44	37
45°	14	18	18	18	14	10
55°	2	2	4	3	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P777689

CATALOG NUMBER: LERS4D08D010-EC4DR300210IC9035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2608.4	2608.4	2608.4	2608.4	2608.4
2.5°	2591.1	2589.3	2590.3	2591.6	2592.1
5°	2523.8	2521.4	2520.9	2526.1	2524.0
7.5°	2388.2	2384.8	2379.5	2391.4	2402.6
10°	2161.1	2157.2	2145.8	2151.4	2160.5
12.5°	1825.7	1813.2	1813.0	1830.9	1828.5
15°	1382.9	1366.3	1375.5	1371.0	1368.6
17.5°	930.0	923.6	935.9	932.2	916.1
20°	669.0	670.6	694.1	682.3	668.1
22.5°	488.2	494.2	522.0	491.6	480.5
25°	325.0	337.3	366.5	328.8	318.4
27.5°	199.9	205.5	235.1	197.3	191.7
30°	124.3	121.5	135.5	116.3	108.3
32.5°	81.6	78.0	82.4	74.0	67.6
35°	54.5	55.7	52.3	51.9	43.8
37.5°	34.1	39.2	34.5	36.9	28.2
40°	22.0	28.4	24.5	27.0	20.7
42.5°	18.0	21.9	20.1	21.4	18.4
45°	14.3	17.8	17.8	17.8	14.5
47.5°	8.0	11.9	15.2	12.1	8.5
50°	4.5	6.0	11.8	6.3	4.8
52.5°	3.1	3.4	8.1	3.6	3.2
55°	2.3	2.4	4.4	2.6	2.4
57.5°	1.8	1.9	2.3	1.9	1.8
60°	1.4	1.4	1.7	1.5	1.4
62.5°	1.0	1.0	1.1	1.0	1.0
65°	0.7	0.7	0.7	0.7	0.7
67.5°	0.4	0.5	0.5	0.5	0.5
70°	0.4	0.2	0.2	0.2	0.4
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)