

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778149

Luminaire Tested: LERS4D10D010-EC4DR600210IC9040-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P778149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D10D010-EC4DR600210IC9040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1144.4 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778149

CATALOG NUMBER: LERS4D10D010-EC4DR600210IC9040-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P778149

CATALOG NUMBER: LERS4D10D010-EC4DR600210IC9040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125136
5°	124836
10°	128975
15°	129110
20°	118796
25°	101050
30°	76985
35°	54447
40°	31963
45°	12902
50°	4300
55°	2076
60°	852
65°	129
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12902 cd/sqm



TEST NUMBER: P778149

CATALOG NUMBER: LERS4D10D010-EC4DR600210IC9040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.8	9.6
10°-20°	316.2	27.6
20°-30°	378.5	33.1
30°-40°	253.1	22.1
40°-50°	75.0	6.6
50°-60°	10.8	0.9
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	804.5	70.3
0°-40°	1057.6	92.4
0°-60°	1143.4	99.9
0°-90°	1144.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1144.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1145	
5°	1138	110
15°	1141	316
25°	838	378
35°	408	253
45°	84	75
55°	11	11
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P778149

CATALOG NUMBER: LERS4D10D010-EC4DR600210IC9040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1145.3
2.5°	1143.8
5°	1138.2
7.5°	1153.6
10°	1162.5
12.5°	1160.9
15°	1141.4
17.5°	1095.4
20°	1021.7
22.5°	933.2
25°	838.2
27.5°	731.1
30°	610.2
32.5°	502.4
35°	408.2
37.5°	313.8
40°	224.1
42.5°	147.8
45°	83.5
47.5°	42.7
50°	25.3
52.5°	16.4
55°	10.9
57.5°	7.0
60°	3.9
62.5°	1.6
65°	0.5
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)