

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843555

Luminaire Tested: **LD4C25DE010B50 EU4C25B50 4LBMLI**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P843555
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25DE010B50 EU4C25B50 4LBMLI
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2501.4 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843555

CATALOG NUMBER: LD4C25DE010B50 EU4C25B50 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P843555

CATALOG NUMBER: LD4C25DE010B50 EU4C25B50 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	484436
5°	476198
10°	437544
15°	366427
20°	293572
25°	235877
30°	175579
35°	100304
40°	47086
45°	19998
50°	6364
55°	3234
60°	2236
65°	1744
70°	1114
75°	0
80°	0
85°	0



TEST NUMBER: P843555

CATALOG NUMBER: LD4C25DE010B50 EU4C25B50 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	357.0	14.3
10°-20°	798.2	31.9
20°-30°	793.6	31.7
30°-40°	432.2	17.3
40°-50°	99.9	4.0
50°-60°	14.1	0.6
60°-70°	5.2	0.2
70°-80°	1.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1948.8	77.9
0°-40°	2380.9	95.2
0°-60°	2494.9	99.7
0°-90°	2501.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2501.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3943	
5°	3861	357
15°	2881	798
25°	1740	794
35°	669	432
45°	115	100
55°	15	14
65°	6	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P843555

CATALOG NUMBER: LD4C25DE010B50 EU4C25B50 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3943.2
2.5°	3934.1
5°	3861.4
7.5°	3713.1
10°	3507.4
12.5°	3204.8
15°	2881.0
17.5°	2560.2
20°	2245.5
22.5°	1988.2
25°	1740.1
27.5°	1504.1
30°	1237.7
32.5°	941.2
35°	668.8
37.5°	450.9
40°	293.6
42.5°	184.6
45°	115.1
47.5°	66.6
50°	33.3
52.5°	18.2
55°	15.1
57.5°	9.1
60°	9.1
62.5°	6.0
65°	6.0
67.5°	3.1
70°	3.1
72.5°	3.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)