

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843241

Luminaire Tested: **LD4C08DE010B35 EU4C08B35 4LBCSMMS**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843241
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08DE010B35 EU4C08B35 4LBCSMMS
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 581.7 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843241

CATALOG NUMBER: LD4C08DE010B35 EU4C08B35 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P843241

CATALOG NUMBER: LD4C08DE010B35 EU4C08B35 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29178
5°	29166
10°	29154
15°	28884
20°	28658
25°	28385
30°	27904
35°	27446
40°	26622
45°	25731
50°	24197
55°	21890
60°	19239
65°	16192
70°	12644
75°	8876
80°	5023
85°	3383



TEST NUMBER: P843241

CATALOG NUMBER: LD4C08DE010B35 EU4C08B35 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.5	3.9
10°-20°	64.1	11.0
20°-30°	96.4	16.6
30°-40°	114.3	19.6
40°-50°	113.7	19.5
50°-60°	91.7	15.8
60°-70°	55.4	9.5
70°-80°	20.6	3.5
80°-90°	3.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.0	31.5
0°-40°	297.3	51.1
0°-60°	502.7	86.4
0°-90°	581.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	581.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	238	
5°	236	23
15°	227	64
25°	209	96
35°	183	114
45°	148	114
55°	102	92
65°	56	55
75°	19	21
85°	2	3
90°	0	



TEST NUMBER: P843241

CATALOG NUMBER: LD4C08DE010B35 EU4C08B35 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	237.5
2.5°	237.5
5°	236.5
7.5°	235.9
10°	233.7
12.5°	230.1
15°	227.1
17.5°	223.5
20°	219.2
22.5°	215.0
25°	209.4
27.5°	203.4
30°	196.7
32.5°	190.4
35°	183.0
37.5°	175.2
40°	166.0
42.5°	157.3
45°	148.1
47.5°	137.8
50°	126.6
52.5°	114.9
55°	102.2
57.5°	91.0
60°	78.3
62.5°	66.9
65°	55.7
67.5°	45.1
70°	35.2
72.5°	26.4
75°	18.7
77.5°	12.0
80°	7.1
82.5°	4.2
85°	2.4
87.5°	1.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)