

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843288

Luminaire Tested: **LD4C10DE010B2750 EU4C10B27 4LBMH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10DE010B2750 EU4C10B27 4LBMH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 872.5 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843288

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B27 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P843288

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B27 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79				79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73				73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67				67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62				62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106281
5°	104750
10°	100360
15°	94793
20°	88497
25°	80329
30°	67071
35°	48592
40°	30407
45°	17391
50°	9059
55°	5076
60°	3243
65°	1919
70°	1401
75°	617
80°	920
85°	0



TEST NUMBER: P843288

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B27 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.6	9.1
10°-20°	208.8	23.9
20°-30°	268.4	30.8
30°-40°	201.9	23.1
40°-50°	81.1	9.3
50°-60°	23.0	2.6
60°-70°	7.3	0.8
70°-80°	2.1	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	556.9	63.8
0°-40°	758.8	87.0
0°-60°	863.0	98.9
0°-90°	872.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	872.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	865	
5°	849	80
15°	745	209
25°	593	268
35°	324	202
45°	100	81
55°	24	23
65°	7	7
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P843288

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B27 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	865.1
2.5°	860.0
5°	849.4
7.5°	829.6
10°	804.5
12.5°	774.3
15°	745.3
17.5°	712.4
20°	676.9
22.5°	638.7
25°	592.6
27.5°	537.3
30°	472.8
32.5°	400.3
35°	324.0
37.5°	252.8
40°	189.6
42.5°	139.6
45°	100.1
47.5°	68.5
50°	47.4
52.5°	32.9
55°	23.7
57.5°	17.1
60°	13.2
62.5°	9.2
65°	6.6
67.5°	5.3
70°	3.9
72.5°	2.6
75°	1.3
77.5°	1.3
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)