

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843256

Luminaire Tested: **LD4C08DE010B40 EU4C08B40 4LBCSMW**

Issue Date: 5/7/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P843256  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C08DE010B40 EU4C08B40 4LBCSMW  
Description: 4in Downlight with BioUp LEDs  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 705.5 lumens  
Efficiency: N/A  
Efficacy: 73.5 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843256

CATALOG NUMBER: LD4C08DE010B40 EU4C08B40 4LBCSMW

### Luminous Intensity Polar Plot





TEST NUMBER: P843256

CATALOG NUMBER: LD4C08DE010B40 EU4C08B40 4LBSCMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	35394
5°	35369
10°	35354
15°	35015
20°	34763
25°	34417
30°	33833
35°	33280
40°	32299
45°	31204
50°	29338
55°	26559
60°	23318
65°	19651
70°	15338
75°	10728
80°	6084
85°	4229



TEST NUMBER: P843256

CATALOG NUMBER: LD4C08DE010B40 EU4C08B40 4LBCSMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	27.3	3.9
10°-20°	77.7	11.0
20°-30°	116.9	16.6
30°-40°	138.6	19.6
40°-50°	137.9	19.5
50°-60°	111.2	15.8
60°-70°	67.2	9.5
70°-80°	25.0	3.5
80°-90°	3.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	221.9	31.5
0°-40°	360.5	51.1
0°-60°	609.6	86.4
0°-90°	705.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	705.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	288	
5°	287	27
15°	275	78
25°	254	117
35°	222	139
45°	180	138
55°	124	111
65°	68	67
75°	23	25
85°	3	4
90°	0	



TEST NUMBER: P843256

CATALOG NUMBER: LD4C08DE010B40 EU4C08B40 4LBCSMW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	288.1
2.5°	288.1
5°	286.8
7.5°	286.0
10°	283.4
12.5°	279.1
15°	275.3
17.5°	271.1
20°	265.9
22.5°	260.8
25°	253.9
27.5°	246.6
30°	238.5
32.5°	230.9
35°	221.9
37.5°	212.5
40°	201.4
42.5°	190.7
45°	179.6
47.5°	167.1
50°	153.5
52.5°	139.4
55°	124.0
57.5°	110.3
60°	94.9
62.5°	81.2
65°	67.6
67.5°	54.7
70°	42.7
72.5°	32.0
75°	22.6
77.5°	14.6
80°	8.6
82.5°	5.2
85°	3.0
87.5°	1.3
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)