

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843302

Luminaire Tested: **LD4C10DE010B2750 EU4C10B30 4LBMH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843302
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10DE010B2750 EU4C10B30 4LBMH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 859.9 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843302

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P843302

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79				79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73				73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67				67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62				62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104745
5°	103221
10°	98913
15°	93419
20°	87202
25°	79163
30°	66092
35°	47887
40°	29974
45°	17131
50°	8926
55°	5012
60°	3194
65°	1890
70°	1401
75°	617
80°	920
85°	0



TEST NUMBER: P843302

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.5	9.1
10°-20°	205.8	23.9
20°-30°	264.5	30.8
30°-40°	199.0	23.1
40°-50°	79.9	9.3
50°-60°	22.7	2.6
60°-70°	7.2	0.8
70°-80°	2.1	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	548.8	63.8
0°-40°	747.8	87.0
0°-60°	850.5	98.9
0°-90°	859.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	859.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	853	
5°	837	78
15°	734	206
25°	584	265
35°	319	199
45°	99	80
55°	23	23
65°	6	7
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P843302

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	852.6
2.5°	847.4
5°	837.0
7.5°	817.6
10°	792.9
12.5°	763.1
15°	734.5
17.5°	702.1
20°	667.0
22.5°	629.4
25°	584.0
27.5°	529.5
30°	465.9
32.5°	394.5
35°	319.3
37.5°	249.2
40°	186.9
42.5°	137.6
45°	98.6
47.5°	67.5
50°	46.7
52.5°	32.5
55°	23.4
57.5°	16.9
60°	13.0
62.5°	9.1
65°	6.5
67.5°	5.2
70°	3.9
72.5°	2.6
75°	1.3
77.5°	1.3
80°	1.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)