

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843304

Luminaire Tested: **LD4C10DE010B2750 EU4C10B30 4LBNH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10DE010B2750 EU4C10B30 4LBNH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 713.9 lumens
Efficiency: N/A
Efficacy: 53.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843304

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P843304

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110114
5°	107673
10°	99549
15°	89324
20°	78639
25°	67668
30°	54488
35°	36279
40°	18876
45°	8548
50°	3708
55°	2485
60°	1597
65°	1134
70°	934
75°	617
80°	0
85°	0



TEST NUMBER: P843304

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.9	11.3
10°-20°	196.2	27.5
20°-30°	227.8	31.9
30°-40°	150.8	21.1
40°-50°	42.3	5.9
50°-60°	10.6	1.5
60°-70°	4.0	0.6
70°-80°	1.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	504.8	70.7
0°-40°	655.6	91.8
0°-60°	708.6	99.2
0°-90°	713.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	713.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	896	
5°	873	81
15°	702	196
25°	499	228
35°	242	151
45°	49	42
55°	12	11
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P843304

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B30 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	896.3
2.5°	892.4
5°	873.1
7.5°	839.3
10°	798.0
12.5°	751.4
15°	702.3
17.5°	654.5
20°	601.5
22.5°	552.3
25°	499.2
27.5°	448.9
30°	384.1
32.5°	315.6
35°	241.9
37.5°	173.3
40°	117.7
42.5°	76.3
45°	49.2
47.5°	29.7
50°	19.4
52.5°	14.2
55°	11.6
57.5°	9.1
60°	6.5
62.5°	5.2
65°	3.9
67.5°	2.6
70°	2.6
72.5°	1.3
75°	1.3
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)