

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760725

Luminaire Tested: LD6D10D010-EU6DR650210IC9027-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P760725
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR650210IC9027-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 926.0 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760725

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9027-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P760725

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9027-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99624
5°	99708
10°	103224
15°	103387
20°	95181
25°	81110
30°	62085
35°	43870
40°	25887
45°	10507
50°	3808
55°	2114
60°	1224
65°	672
70°	703
75°	549
80°	566
85°	501

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10507 cd/sqm



TEST NUMBER: P760725

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9027-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.8	9.5
10°-20°	253.3	27.3
20°-30°	303.9	32.8
30°-40°	204.2	22.1
40°-50°	61.1	6.6
50°-60°	10.8	1.2
60°-70°	3.1	0.3
70°-80°	1.5	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	644.9	69.6
0°-40°	849.2	91.7
0°-60°	921.0	99.5
0°-90°	926.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	926.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	912	
5°	909	88
15°	914	253
25°	673	304
35°	329	204
45°	68	61
55°	11	11
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P760725

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9027-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	911.8
2.5°	915.7
5°	909.1
7.5°	922.9
10°	930.4
12.5°	928.5
15°	914.0
17.5°	878.5
20°	818.6
22.5°	748.2
25°	672.8
27.5°	587.6
30°	492.1
32.5°	405.6
35°	328.9
37.5°	253.1
40°	181.5
42.5°	118.5
45°	68.0
47.5°	36.0
50°	22.4
52.5°	15.5
55°	11.1
57.5°	8.0
60°	5.6
62.5°	3.6
65°	2.6
67.5°	2.3
70°	2.2
72.5°	1.7
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)