

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843331

Luminaire Tested: **LD4C10DE010B2750 EU4C10B40 4LBMLI**

Issue Date: 2/17/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P843331  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C10DE010B2750 EU4C10B40 4LBMLI  
Description: 4in Downlight with BioUp LEDs  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1091.4 lumens  
Efficiency: N/A  
Efficacy: 82.1 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843331

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P843331

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	211394
5°	207799
10°	190928
15°	159887
20°	128097
25°	102926
30°	76618
35°	43778
40°	20544
45°	8722
50°	2771
55°	1414
60°	958
65°	756
70°	467
75°	0
80°	0
85°	0



TEST NUMBER: P843331

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.8	14.3
10°-20°	348.3	31.9
20°-30°	346.3	31.7
30°-40°	188.6	17.3
40°-50°	43.6	4.0
50°-60°	6.1	0.6
60°-70°	2.2	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.4	77.9
0°-40°	1039.0	95.2
0°-60°	1088.7	99.7
0°-90°	1091.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1091.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1721	
5°	1685	156
15°	1257	348
25°	759	346
35°	292	189
45°	50	44
55°	7	6
65°	3	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P843331

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBMLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1720.7
2.5°	1716.6
5°	1685.0
7.5°	1620.3
10°	1530.5
12.5°	1398.5
15°	1257.1
17.5°	1117.2
20°	979.8
22.5°	867.6
25°	759.3
27.5°	656.4
30°	540.1
32.5°	410.7
35°	291.9
37.5°	196.7
40°	128.1
42.5°	80.5
45°	50.2
47.5°	29.1
50°	14.5
52.5°	7.9
55°	6.6
57.5°	3.9
60°	3.9
62.5°	2.6
65°	2.6
67.5°	1.3
70°	1.3
72.5°	1.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)