

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760802

Luminaire Tested: LD6D10D010-EU6DR700210IC9027-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P760802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR700210IC9027-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1016.1 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760802

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9027-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P760802

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9027-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124809
5°	121096
10°	117725
15°	116180
20°	108494
25°	81508
30°	57619
35°	20408
40°	10726
45°	11434
50°	11831
55°	12058
60°	12128
65°	11893
70°	11213
75°	10385
80°	9249
85°	7522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 12140 cd/sqm



TEST NUMBER: P760802

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9027-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.1	10.2
10°-20°	285.7	28.1
20°-30°	314.6	31.0
30°-40°	120.2	11.8
40°-50°	56.8	5.6
50°-60°	56.4	5.6
60°-70°	45.2	4.4
70°-80°	26.0	2.6
80°-90°	7.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	704.4	69.3
0°-40°	824.6	81.2
0°-60°	937.9	92.3
0°-90°	1016.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1016.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1142	
5°	1104	104
15°	1027	286
25°	676	315
35°	153	120
45°	74	57
55°	63	56
65°	46	45
75°	25	26
85°	6	7
90°	0	



TEST NUMBER: P760802

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9027-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1142.3
2.5°	1130.4
5°	1104.1
7.5°	1082.2
10°	1061.1
12.5°	1043.2
15°	1027.1
17.5°	988.2
20°	933.1
22.5°	814.0
25°	676.1
27.5°	588.5
30°	456.7
32.5°	295.0
35°	153.0
37.5°	82.7
40°	75.2
42.5°	74.7
45°	74.0
47.5°	72.4
50°	69.6
52.5°	66.6
55°	63.3
57.5°	59.7
60°	55.5
62.5°	50.8
65°	46.0
67.5°	40.5
70°	35.1
72.5°	29.7
75°	24.6
77.5°	19.4
80°	14.7
82.5°	10.3
85°	6.0
87.5°	2.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)