

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843336

Luminaire Tested: **LD4C10DE010B2750 EU4C10B40 4LBWH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10DE010B2750 EU4C10B40 4LBWH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 971.9 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843336

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P843336

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76968
5°	77262
10°	77506
15°	77495
20°	77070
25°	75273
30°	70348
35°	60920
40°	47599
45°	34140
50°	22171
55°	13280
60°	7764
65°	4971
70°	3305
75°	2516
80°	1839
85°	0



TEST NUMBER: P843336

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.7	6.1
10°-20°	171.9	17.7
20°-30°	253.7	26.1
30°-40°	250.3	25.8
40°-50°	153.2	15.8
50°-60°	58.7	6.0
60°-70°	18.3	1.9
70°-80°	5.4	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	485.2	49.9
0°-40°	735.6	75.7
0°-60°	947.5	97.5
0°-90°	971.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	971.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	626	
5°	626	60
15°	609	172
25°	555	254
35°	406	250
45°	196	153
55°	62	59
65°	17	18
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P843336

CATALOG NUMBER: LD4C10DE010B2750 EU4C10B40 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	626.5
2.5°	627.8
5°	626.5
7.5°	625.2
10°	621.3
12.5°	616.0
15°	609.3
17.5°	601.4
20°	589.5
22.5°	576.4
25°	555.3
27.5°	528.8
30°	495.9
32.5°	455.0
35°	406.2
37.5°	352.1
40°	296.8
42.5°	245.3
45°	196.5
47.5°	152.9
50°	116.0
52.5°	85.8
55°	62.0
57.5°	43.5
60°	31.6
62.5°	23.8
65°	17.1
67.5°	13.2
70°	9.2
72.5°	6.6
75°	5.3
77.5°	2.6
80°	2.6
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)