

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760660

Luminaire Tested: LD6D10D010-EU6DR600210IC9030-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P760660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR600210IC9030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1094.4 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.84
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760660

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P760660

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142006
5°	145499
10°	147259
15°	140285
20°	123691
25°	100049
30°	67674
35°	33906
40°	5506
45°	5377
50°	5490
55°	5581
60°	5725
65°	5869
70°	6006
75°	6079
80°	5852
85°	4889

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 6079 cd/sqm



TEST NUMBER: P760660

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.8	11.6
10°-20°	343.0	31.3
20°-30°	369.1	33.7
30°-40°	160.4	14.7
40°-50°	26.9	2.5
50°-60°	26.2	2.4
60°-70°	22.4	2.0
70°-80°	15.0	1.4
80°-90°	4.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	838.9	76.7
0°-40°	999.4	91.3
0°-60°	1052.5	96.2
0°-90°	1094.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1094.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1300	
5°	1327	127
15°	1240	343
25°	830	369
35°	254	160
45°	35	27
55°	29	26
65°	23	22
75°	14	15
85°	4	5
90°	0	



TEST NUMBER: P760660

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1299.7
2.5°	1336.3
5°	1326.6
7.5°	1329.6
10°	1327.3
12.5°	1299.9
15°	1240.2
17.5°	1160.0
20°	1063.8
22.5°	960.8
25°	829.9
27.5°	663.8
30°	536.4
32.5°	413.4
35°	254.2
37.5°	108.7
40°	38.6
42.5°	35.5
45°	34.8
47.5°	33.6
50°	32.3
52.5°	30.8
55°	29.3
57.5°	27.7
60°	26.2
62.5°	24.5
65°	22.7
67.5°	20.8
70°	18.8
72.5°	16.6
75°	14.4
77.5°	11.9
80°	9.3
82.5°	6.6
85°	3.9
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)