

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760661

Luminaire Tested: LD6D10D010-EU6DR600210IC9030-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P760661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR600210IC9030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 943.9 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760661

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P760661

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122481
5°	125494
10°	127011
15°	120988
20°	106680
25°	86282
30°	58363
35°	29251
40°	4750
45°	4651
50°	4725
55°	4819
60°	4939
65°	5041
70°	5175
75°	5235
80°	5034
85°	4262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 5235 cd/sqm



TEST NUMBER: P760661

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.4	11.6
10°-20°	295.9	31.3
20°-30°	318.3	33.7
30°-40°	138.4	14.7
40°-50°	23.3	2.5
50°-60°	22.6	2.4
60°-70°	19.3	2.0
70°-80°	12.9	1.4
80°-90°	3.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	723.6	76.7
0°-40°	861.9	91.3
0°-60°	907.8	96.2
0°-90°	943.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	943.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1121	
5°	1144	109
15°	1070	296
25°	716	318
35°	219	138
45°	30	23
55°	25	23
65°	20	19
75°	12	13
85°	3	4
90°	0	



TEST NUMBER: P760661

CATALOG NUMBER: LD6D10D010-EU6DR600210IC9030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1121.0
2.5°	1152.5
5°	1144.2
7.5°	1146.8
10°	1144.8
12.5°	1121.2
15°	1069.6
17.5°	1000.5
20°	917.5
22.5°	828.7
25°	715.7
27.5°	572.5
30°	462.6
32.5°	356.5
35°	219.3
37.5°	93.8
40°	33.3
42.5°	30.7
45°	30.1
47.5°	29.0
50°	27.8
52.5°	26.5
55°	25.3
57.5°	23.9
60°	22.6
62.5°	21.1
65°	19.5
67.5°	17.9
70°	16.2
72.5°	14.3
75°	12.4
77.5°	10.2
80°	8.0
82.5°	5.7
85°	3.4
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)