

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843353

Luminaire Tested: **LD4C15DE010B2750 EU4C15B27 4LBCSMMS**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843353
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15DE010B2750 EU4C15B27 4LBCSMMS
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1060.8 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843353

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P843353

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87																			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74																			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63																			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55																			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48																			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33																			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30																			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53220
5°	53201
10°	53168
15°	52668
20°	52282
25°	51768
30°	50885
35°	50047
40°	48561
45°	46910
50°	44112
55°	39925
60°	35087
65°	29506
70°	23061
75°	16186
80°	9127
85°	6202



TEST NUMBER: P843353

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.0	3.9
10°-20°	116.9	11.0
20°-30°	175.8	16.6
30°-40°	208.4	19.6
40°-50°	207.3	19.5
50°-60°	167.2	15.8
60°-70°	101.1	9.5
70°-80°	37.6	3.5
80°-90°	5.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	333.8	31.5
0°-40°	542.1	51.1
0°-60°	916.6	86.4
0°-90°	1060.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1060.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	433	
5°	431	41
15°	414	117
25°	382	176
35°	334	208
45°	270	207
55°	186	167
65°	102	101
75°	34	38
85°	4	6
90°	0	



TEST NUMBER: P843353

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	433.2
2.5°	433.2
5°	431.4
7.5°	430.0
10°	426.2
12.5°	419.8
15°	414.1
17.5°	407.6
20°	399.9
22.5°	392.2
25°	381.9
27.5°	370.9
30°	358.7
32.5°	347.1
35°	333.7
37.5°	319.5
40°	302.8
42.5°	286.7
45°	270.0
47.5°	251.3
50°	230.8
52.5°	209.5
55°	186.4
57.5°	165.9
60°	142.8
62.5°	122.2
65°	101.5
67.5°	82.3
70°	64.2
72.5°	48.2
75°	34.1
77.5°	21.9
80°	12.9
82.5°	7.7
85°	4.4
87.5°	1.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)