

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843364

Luminaire Tested: **LD4C15DE010B2750 EU4C15B27 4LBWH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843364
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15DE010B2750 EU4C15B27 4LBWH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1254.3 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843364

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P843364

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82				82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61				61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55				55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50				50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43				43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39				39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99327
5°	99706
10°	100011
15°	100020
20°	99465
25°	97124
30°	90790
35°	78618
40°	61423
45°	44061
50°	28631
55°	17135
60°	10025
65°	6424
70°	4310
75°	3228
80°	2405
85°	0



TEST NUMBER: P843364

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	6.1
10°-20°	221.9	17.7
20°-30°	327.4	26.1
30°-40°	323.1	25.8
40°-50°	197.7	15.8
50°-60°	75.8	6.0
60°-70°	23.7	1.9
70°-80°	7.0	0.6
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	626.2	49.9
0°-40°	949.3	75.7
0°-60°	1222.8	97.5
0°-90°	1254.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1254.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	808	
5°	808	77
15°	786	222
25°	716	327
35°	524	323
45°	254	198
55°	80	76
65°	22	24
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P843364

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B27 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	808.5
2.5°	810.3
5°	808.5
7.5°	806.8
10°	801.7
12.5°	794.9
15°	786.4
17.5°	776.1
20°	760.8
22.5°	743.8
25°	716.5
27.5°	682.5
30°	640.0
32.5°	587.2
35°	524.2
37.5°	454.5
40°	383.0
42.5°	316.5
45°	253.6
47.5°	197.4
50°	149.8
52.5°	110.6
55°	80.0
57.5°	56.2
60°	40.8
62.5°	30.7
65°	22.1
67.5°	17.0
70°	12.0
72.5°	8.6
75°	6.8
77.5°	3.4
80°	3.4
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)