

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843366

Luminaire Tested: **LD4C15DE010B2750 EU4C15B30 4LBCSMB**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843366
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15DE010B2750 EU4C15B30 4LBCSMB
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1021.6 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843366

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B30 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P843366

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B30 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 110 | 106 | 102 | 99 | 108 | 104 | 100 | 97 | 100 | 97 | 94 | 96 | 93 | 91 | 92 | 90 | 89 | 87 | | | | | | | | | | | | | | | | | | | |
| 2 | 101 | 94 | 87 | 82 | 99 | 92 | 86 | 81 | 88 | 84 | 79 | 85 | 81 | 78 | 82 | 79 | 76 | 74 | | | | | | | | | | | | | | | | | | | |
| 3 | 93 | 83 | 75 | 70 | 90 | 81 | 74 | 69 | 79 | 73 | 68 | 76 | 71 | 67 | 73 | 69 | 65 | 63 | | | | | | | | | | | | | | | | | | | |
| 4 | 85 | 74 | 66 | 60 | 83 | 73 | 65 | 59 | 70 | 64 | 58 | 68 | 62 | 58 | 66 | 61 | 57 | 55 | | | | | | | | | | | | | | | | | | | |
| 5 | 79 | 66 | 58 | 52 | 77 | 65 | 57 | 51 | 63 | 56 | 51 | 61 | 55 | 50 | 60 | 54 | 50 | 48 | | | | | | | | | | | | | | | | | | | |
| 6 | 73 | 60 | 52 | 45 | 71 | 59 | 51 | 45 | 57 | 50 | 45 | 56 | 49 | 44 | 54 | 49 | 44 | 42 | | | | | | | | | | | | | | | | | | | |
| 7 | 68 | 55 | 46 | 40 | 66 | 54 | 46 | 40 | 52 | 45 | 40 | 51 | 44 | 40 | 50 | 44 | 39 | 37 | | | | | | | | | | | | | | | | | | | |
| 8 | 63 | 50 | 42 | 36 | 61 | 49 | 41 | 36 | 48 | 41 | 36 | 47 | 40 | 36 | 46 | 40 | 35 | 33 | | | | | | | | | | | | | | | | | | | |
| 9 | 59 | 46 | 38 | 33 | 57 | 45 | 38 | 32 | 44 | 37 | 32 | 43 | 37 | 32 | 42 | 36 | 32 | 30 | | | | | | | | | | | | | | | | | | | |
| 10 | 55 | 42 | 35 | 30 | 54 | 42 | 34 | 30 | 41 | 34 | 29 | 40 | 34 | 29 | 39 | 33 | 29 | 27 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 51254 |
| 5° | 51228 |
| 10° | 51209 |
| 15° | 50710 |
| 20° | 50347 |
| 25° | 49843 |
| 30° | 48998 |
| 35° | 48187 |
| 40° | 46765 |
| 45° | 45190 |
| 50° | 42487 |
| 55° | 38447 |
| 60° | 33785 |
| 65° | 28430 |
| 70° | 22234 |
| 75° | 15569 |
| 80° | 8773 |
| 85° | 6061 |



TEST NUMBER: P843366

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B30 4LBCSMB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 39.5 | 3.9 |
| 10°-20° | 112.6 | 11.0 |
| 20°-30° | 169.3 | 16.6 |
| 30°-40° | 200.7 | 19.6 |
| 40°-50° | 199.7 | 19.5 |
| 50°-60° | 161.0 | 15.8 |
| 60°-70° | 97.4 | 9.5 |
| 70°-80° | 36.1 | 3.5 |
| 80°-90° | 5.4 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 321.4 | 31.5 |
| 0°-40° | 522.1 | 51.1 |
| 0°-60° | 882.8 | 86.4 |
| 0°-90° | 1021.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1021.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 417 | |
| 5° | 415 | 40 |
| 15° | 399 | 113 |
| 25° | 368 | 169 |
| 35° | 321 | 201 |
| 45° | 260 | 200 |
| 55° | 180 | 161 |
| 65° | 98 | 97 |
| 75° | 33 | 36 |
| 85° | 4 | 5 |
| 90° | 0 | |



TEST NUMBER: P843366

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B30 4LBCSMB

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 417.2 |
| 2.5° | 417.2 |
| 5° | 415.4 |
| 7.5° | 414.2 |
| 10° | 410.5 |
| 12.5° | 404.3 |
| 15° | 398.7 |
| 17.5° | 392.6 |
| 20° | 385.1 |
| 22.5° | 377.7 |
| 25° | 367.7 |
| 27.5° | 357.2 |
| 30° | 345.4 |
| 32.5° | 334.3 |
| 35° | 321.3 |
| 37.5° | 307.8 |
| 40° | 291.6 |
| 42.5° | 276.1 |
| 45° | 260.1 |
| 47.5° | 242.1 |
| 50° | 222.3 |
| 52.5° | 201.8 |
| 55° | 179.5 |
| 57.5° | 159.8 |
| 60° | 137.5 |
| 62.5° | 117.6 |
| 65° | 97.8 |
| 67.5° | 79.2 |
| 70° | 61.9 |
| 72.5° | 46.4 |
| 75° | 32.8 |
| 77.5° | 21.0 |
| 80° | 12.4 |
| 82.5° | 7.4 |
| 85° | 4.3 |
| 87.5° | 1.8 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)