

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760828

Luminaire Tested: LD6D10D010-EU6DR700210IC9035-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P760828
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR700210IC9035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1107.5 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760828
CATALOG NUMBER: LD6D10D010-EU6DR700210IC9035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P760828

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136051
5°	132009
10°	128332
15°	126644
20°	118261
25°	88838
30°	62804
35°	22248
40°	11696
45°	12454
50°	12901
55°	13144
60°	13221
65°	12953
70°	12235
75°	11314
80°	10067
85°	8149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 13221 cd/sqm



TEST NUMBER: P760828

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.5	10.3
10°-20°	311.4	28.1
20°-30°	343.0	31.0
30°-40°	131.0	11.8
40°-50°	61.8	5.6
50°-60°	61.5	5.6
60°-70°	49.3	4.4
70°-80°	28.3	2.6
80°-90°	7.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	767.9	69.3
0°-40°	898.9	81.2
0°-60°	1022.2	92.3
0°-90°	1107.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1107.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1245	
5°	1204	114
15°	1120	311
25°	737	343
35°	167	131
45°	81	62
55°	69	61
65°	50	49
75°	27	28
85°	6	8
90°	0	



TEST NUMBER: P760828

CATALOG NUMBER: LD6D10D010-EU6DR700210IC9035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1245.2
2.5°	1232.2
5°	1203.6
7.5°	1179.7
10°	1156.7
12.5°	1137.1
15°	1119.6
17.5°	1077.2
20°	1017.1
22.5°	887.4
25°	736.9
27.5°	641.5
30°	497.8
32.5°	321.5
35°	166.8
37.5°	90.1
40°	82.0
42.5°	81.4
45°	80.6
47.5°	78.8
50°	75.9
52.5°	72.5
55°	69.0
57.5°	65.0
60°	60.5
62.5°	55.4
65°	50.1
67.5°	44.2
70°	38.3
72.5°	32.3
75°	26.8
77.5°	21.1
80°	16.0
82.5°	11.2
85°	6.5
87.5°	2.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)