

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843381

Luminaire Tested: **LD4C15DE010B2750 EU4C15B35 4LBCSMMS**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843381
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15DE010B2750 EU4C15B35 4LBCSMMS
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1072.4 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843381

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P843381

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53810
5°	53781
10°	53754
15°	53241
20°	52844
25°	52324
30°	51452
35°	50587
40°	49090
45°	47431
50°	44590
55°	40375
60°	35456
65°	29854
70°	23312
75°	16329
80°	9197
85°	6343



TEST NUMBER: P843381

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.5	3.9
10°-20°	118.2	11.0
20°-30°	177.7	16.6
30°-40°	210.6	19.6
40°-50°	209.6	19.5
50°-60°	169.0	15.8
60°-70°	102.2	9.5
70°-80°	37.9	3.5
80°-90°	5.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	337.4	31.5
0°-40°	548.0	51.1
0°-60°	926.6	86.4
0°-90°	1072.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1072.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	438	
5°	436	42
15°	419	118
25°	386	178
35°	337	211
45°	273	210
55°	188	169
65°	103	102
75°	34	38
85°	4	6
90°	0	



TEST NUMBER: P843381

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	438.0
2.5°	438.0
5°	436.1
7.5°	434.8
10°	430.9
12.5°	424.4
15°	418.6
17.5°	412.1
20°	404.2
22.5°	396.5
25°	386.0
27.5°	374.9
30°	362.7
32.5°	350.9
35°	337.3
37.5°	323.0
40°	306.1
42.5°	289.9
45°	273.0
47.5°	254.0
50°	233.3
52.5°	211.8
55°	188.5
57.5°	167.7
60°	144.3
62.5°	123.5
65°	102.7
67.5°	83.1
70°	64.9
72.5°	48.8
75°	34.4
77.5°	22.1
80°	13.0
82.5°	7.8
85°	4.5
87.5°	1.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)