

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760062

Luminaire Tested: LD6D10D010-EU6DR200210IC9040-6LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR200210IC9040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1254.6 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760062

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P760062

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	780198
5°	703881
10°	395058
15°	200813
20°	85019
25°	39253
30°	20779
35°	11191
40°	5990
45°	3538
50°	2057
55°	1086
60°	699
65°	491
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3538 cd/sqm



TEST NUMBER: P760062

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9040-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	508.4	40.5
10°-20°	500.6	39.9
20°-30°	163.5	13.0
30°-40°	55.7	4.4
40°-50°	18.7	1.5
50°-60°	5.6	0.4
60°-70°	1.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1172.6	93.5
0°-40°	1228.2	97.9
0°-60°	1252.6	99.8
0°-90°	1254.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1254.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7141	
5°	6418	508
15°	1775	501
25°	326	164
35°	84	56
45°	23	19
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P760062

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7140.7
0.5°	7140.7
1°	7131.8
1.5°	7114.0
2°	7081.6
2.5°	7038.3
3°	6977.3
3.5°	6892.1
4°	6765.5
4.5°	6611.7
5°	6417.7
5.5°	6162.7
6°	5901.4
6.5°	5601.9
7°	5308.8
7.5°	4965.4
8°	4658.9
8.5°	4350.5
9°	4065.7
9.5°	3804.3
10°	3560.8
12.5°	2556.8
15°	1775.3
17.5°	1159.8
20°	731.2
22.5°	473.7
25°	325.6
27.5°	228.9
30°	164.7
32.5°	118.3
35°	83.9
37.5°	58.5
40°	42.0
42.5°	30.5
45°	22.9
47.5°	17.8
50°	12.1
52.5°	7.6
55°	5.7
57.5°	4.5
60°	3.2
62.5°	2.5
65°	1.9



TEST NUMBER: P760062

CATALOG NUMBER: LD6D10D010-EU6DR200210IC9040-6LBDP1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.3
70°		0.6

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)