

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843393

Luminaire Tested: **LD4C15DE010B2750 EU4C15B35 4LBWLI**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843393
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15DE010B2750 EU4C15B35 4LBWLI
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1502.9 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843393

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P843393

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																																				
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																																				
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77																																				
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70																																				
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64																																				
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58																																				
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54																																				
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49																																				
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45																																				
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113123
5°	115035
10°	120245
15°	127632
20°	133209
25°	132070
30°	122821
35°	105073
40°	80043
45°	46945
50°	20049
55°	5912
60°	1695
65°	1017
70°	611
75°	807
80°	0
85°	0



TEST NUMBER: P843393

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	6.0
10°-20°	284.2	18.9
20°-30°	443.3	29.5
30°-40°	431.4	28.7
40°-50°	215.4	14.3
50°-60°	33.4	2.2
60°-70°	4.1	0.3
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	817.6	54.4
0°-40°	1248.9	83.1
0°-60°	1497.8	99.7
0°-90°	1502.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1502.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	921	
5°	933	90
15°	1004	284
25°	974	443
35°	701	431
45°	270	215
55°	28	33
65°	4	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P843393

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B35 4LBWLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	920.8
2.5°	924.3
5°	932.8
7.5°	946.7
10°	963.9
12.5°	986.2
15°	1003.5
17.5°	1017.2
20°	1018.9
22.5°	1006.9
25°	974.3
27.5°	926.0
30°	865.8
32.5°	790.1
35°	700.6
37.5°	602.4
40°	499.1
42.5°	389.0
45°	270.2
47.5°	173.9
50°	104.9
52.5°	56.8
55°	27.6
57.5°	12.1
60°	6.9
62.5°	5.2
65°	3.5
67.5°	3.5
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)