

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843406

Luminaire Tested: **LD4C15DE010B2750 EU4C15B40 4LBWH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15DE010B2750 EU4C15B40 4LBWH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1258.6 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843406

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B40 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P843406

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B40 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99659
5°	100039
10°	100348
15°	100351
20°	99805
25°	97463
30°	91102
35°	78888
40°	61616
45°	44217
50°	28726
55°	17199
60°	10049
65°	6453
70°	4310
75°	3275
80°	2405
85°	0



TEST NUMBER: P843406

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B40 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	6.1
10°-20°	222.6	17.7
20°-30°	328.5	26.1
30°-40°	324.1	25.8
40°-50°	198.4	15.8
50°-60°	76.1	6.0
60°-70°	23.8	1.9
70°-80°	7.0	0.6
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.3	49.9
0°-40°	952.5	75.7
0°-60°	1226.9	97.5
0°-90°	1258.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1258.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	811	
5°	811	77
15°	789	223
25°	719	328
35°	526	324
45°	254	198
55°	80	76
65°	22	24
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P843406

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B40 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	811.2
2.5°	812.9
5°	811.2
7.5°	809.5
10°	804.4
12.5°	797.6
15°	789.0
17.5°	778.7
20°	763.4
22.5°	746.4
25°	719.0
27.5°	684.8
30°	642.2
32.5°	589.2
35°	526.0
37.5°	455.9
40°	384.2
42.5°	317.6
45°	254.5
47.5°	198.1
50°	150.3
52.5°	111.1
55°	80.3
57.5°	56.4
60°	40.9
62.5°	30.8
65°	22.2
67.5°	17.1
70°	12.0
72.5°	8.6
75°	6.9
77.5°	3.4
80°	3.4
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)