

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843410

Luminaire Tested: **LD4C15DE010B2750 EU4C15B50 4LBCSMW**

Issue Date: 5/7/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P843410  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C15DE010B2750 EU4C15B50 4LBSCMW  
Description: 4in Downlight with BioUp LEDs  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1387.6 lumens  
Efficiency: N/A  
Efficacy: 81.6 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 17  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843410

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B50 4LBCSMW

### Luminous Intensity Polar Plot





TEST NUMBER: P843410

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B50 4LBCSMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	75	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34				34
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	69621
5°	69579
10°	69547
15°	68885
20°	68389
25°	67709
30°	66560
35°	65465
40°	63524
45°	61365
50°	57720
55°	52219
60°	45873
65°	38604
70°	30173
75°	21123
80°	11886
85°	8176



TEST NUMBER: P843410

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B50 4LBCSMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.7	3.9
10°-20°	152.9	11.0
20°-30°	230.0	16.6
30°-40°	272.6	19.6
40°-50°	271.2	19.5
50°-60°	218.7	15.8
60°-70°	132.2	9.5
70°-80°	49.1	3.5
80°-90°	7.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	436.6	31.5
0°-40°	709.1	51.1
0°-60°	1199.0	86.4
0°-90°	1387.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1387.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	567	
5°	564	54
15°	542	153
25°	500	230
35°	436	273
45°	353	271
55°	244	219
65°	133	132
75°	44	49
85°	6	7
90°	0	



TEST NUMBER: P843410

CATALOG NUMBER: LD4C15DE010B2750 EU4C15B50 4LBCSMW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	566.7
2.5°	566.7
5°	564.2
7.5°	562.6
10°	557.5
12.5°	549.1
15°	541.6
17.5°	533.2
20°	523.1
22.5°	513.0
25°	499.5
27.5°	485.1
30°	469.2
32.5°	454.0
35°	436.5
37.5°	418.0
40°	396.1
42.5°	375.0
45°	353.2
47.5°	328.7
50°	302.0
52.5°	274.1
55°	243.8
57.5°	217.0
60°	186.7
62.5°	159.8
65°	132.8
67.5°	107.6
70°	84.0
72.5°	63.0
75°	44.5
77.5°	28.7
80°	16.8
82.5°	10.0
85°	5.8
87.5°	2.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)