

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757007

Luminaire Tested: LD6D02D010-EU6DR200210IC9035-6LBDP1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P757007  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D02D010-EU6DR200210IC9035-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 425.7 lumens  
Efficiency: N/A  
Efficacy: 83.5 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P757007

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P757007

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	98	97															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	95															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	96	95															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	98	96	95															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	98	96	95															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	98	96	95															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	98	96	95															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	98	96	95															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	98	96	95															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	98	96	95															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	264761
5°	238868
10°	134067
15°	68152
20°	28847
25°	13321
30°	7053
35°	3801
40°	2025
45°	1205
50°	697
55°	362
60°	240
65°	155
70°	64
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1205 cd/sqm



TEST NUMBER: P757007

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.5	40.5
10°-20°	169.9	39.9
20°-30°	55.5	13.0
30°-40°	18.9	4.4
40°-50°	6.4	1.5
50°-60°	1.9	0.4
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	397.9	93.5
0°-40°	416.8	97.9
0°-60°	425.1	99.8
0°-90°	425.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	425.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2423	
5°	2178	173
15°	602	170
25°	110	56
35°	28	19
45°	8	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P757007

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2423.2
0.5°	2423.2
1°	2420.2
1.5°	2414.1
2°	2403.1
2.5°	2388.5
3°	2367.7
3.5°	2338.8
4°	2295.9
4.5°	2243.7
5°	2177.9
5.5°	2091.3
6°	2002.7
6.5°	1901.0
7°	1801.5
7.5°	1685.0
8°	1581.0
8.5°	1476.4
9°	1379.7
9.5°	1291.0
10°	1208.4
12.5°	867.6
15°	602.5
17.5°	393.6
20°	248.1
22.5°	160.8
25°	110.5
27.5°	77.7
30°	55.9
32.5°	40.1
35°	28.5
37.5°	19.9
40°	14.2
42.5°	10.4
45°	7.8
47.5°	6.0
50°	4.1
52.5°	2.6
55°	1.9
57.5°	1.5
60°	1.1
62.5°	0.9
65°	0.6



TEST NUMBER: P757007

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBDP1LI

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.4
70°		0.2

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)