

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843527

Luminaire Tested: **LD4C25DE010B2750 EU4C25B35 4LBMLI**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25DE010B2750 EU4C25B35 4LBMLI
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2362.7 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843527

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P843527

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88				88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83				83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78				78
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73				73
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69				69
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65				65
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62				62
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58				58
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56				56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	457605
5°	449820
10°	413305
15°	346127
20°	277308
25°	222810
30°	165862
35°	94755
40°	44472
45°	18886
50°	6001
55°	3063
60°	2113
65°	1657
70°	1042
75°	0
80°	0
85°	0



TEST NUMBER: P843527

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.2	14.3
10°-20°	754.0	31.9
20°-30°	749.6	31.7
30°-40°	408.2	17.3
40°-50°	94.3	4.0
50°-60°	13.3	0.6
60°-70°	4.9	0.2
70°-80°	1.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1840.8	77.9
0°-40°	2249.0	95.2
0°-60°	2356.7	99.7
0°-90°	2362.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2362.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3725	
5°	3648	337
15°	2721	754
25°	1644	750
35°	632	408
45°	109	94
55°	14	13
65°	6	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P843527

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B35 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3724.8
2.5°	3716.1
5°	3647.5
7.5°	3507.5
10°	3313.1
12.5°	3027.3
15°	2721.4
17.5°	2418.4
20°	2121.1
22.5°	1878.1
25°	1643.7
27.5°	1420.7
30°	1169.2
32.5°	889.0
35°	631.8
37.5°	425.9
40°	277.3
42.5°	174.3
45°	108.7
47.5°	62.9
50°	31.4
52.5°	17.1
55°	14.3
57.5°	8.6
60°	8.6
62.5°	5.7
65°	5.7
67.5°	2.9
70°	2.9
72.5°	2.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)