

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757012

Luminaire Tested: LD6D02D010-EU6DR200210IC9035-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P757012
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR200210IC9035-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 405.4 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757012

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P757012

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94	94	92	91	91	89	88	86	85	85	83	83	81	79	77	77								
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	92	91	89	88	86	85	85	83	83	81	79	77	77	75	75	73	73									
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	89	88	86	85	85	83	83	81	79	77	77	75	75	73	73	71	71									
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	86	85	85	83	83	81	79	77	77	75	75	73	73	71	71	69	69									
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	83	83	81	81	79	79	77	77	75	75	73	73	71	71	69	69	67	67								
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	81	81	79	79	77	77	75	75	73	73	71	71	69	69	67	67	65	65								
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	79	79	77	77	75	75	73	73	71	71	69	69	67	67	65	65	63	63								
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	77	77	75	75	73	73	71	71	69	69	67	67	65	65	63	63	61	61								
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	75	75	73	73	71	71	69	69	67	67	65	65	63	63	61	61	59	59								
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	73	73	71	71	69	69	67	67	65	65	63	63	61	61	59	59	57	57								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	252152
5°	227494
10°	127677
15°	64905
20°	27475
25°	12682
30°	6712
35°	3615
40°	1940
45°	1143
50°	663
55°	343
60°	219
65°	155
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1143 cd/sqm



TEST NUMBER: P757012

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.3	40.5
10°-20°	161.8	39.9
20°-30°	52.9	13.0
30°-40°	18.0	4.4
40°-50°	6.1	1.5
50°-60°	1.8	0.4
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.0	93.5
0°-40°	396.9	97.9
0°-60°	404.8	99.8
0°-90°	405.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	405.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2308	
5°	2074	164
15°	574	162
25°	105	53
35°	27	18
45°	7	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P757012

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2307.8
0.5°	2307.8
1°	2304.9
1.5°	2299.2
2°	2288.7
2.5°	2274.7
3°	2255.0
3.5°	2227.5
4°	2186.6
4.5°	2136.8
5°	2074.2
5.5°	1991.7
6°	1907.3
6.5°	1810.5
7°	1715.8
7.5°	1604.8
8°	1505.7
8.5°	1406.1
9°	1314.0
9.5°	1229.5
10°	1150.8
12.5°	826.3
15°	573.8
17.5°	374.8
20°	236.3
22.5°	153.1
25°	105.2
27.5°	74.0
30°	53.2
32.5°	38.2
35°	27.1
37.5°	18.9
40°	13.6
42.5°	9.9
45°	7.4
47.5°	5.8
50°	3.9
52.5°	2.5
55°	1.8
57.5°	1.4
60°	1.0
62.5°	0.8
65°	0.6



TEST NUMBER: P757012
CATALOG NUMBER: LD6D02D010-EU6DR200210IC9035-6LBS1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.4
70°		0.2

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)