

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757019

Luminaire Tested: LD6D02D010-EU6DR200210IC9040-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P757019
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR200210IC9040-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 416.6 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757019

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P757019

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97	94															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	96	94															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	96	94															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	96	94	92															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	94	92	90															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	92	90	88															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	90	88	86															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	88	86	84															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	86	84	82															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	84	82	80															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	259123
5°	233779
10°	131205
15°	66693
20°	28243
25°	13032
30°	6901
35°	3721
40°	1983
45°	1174
50°	680
55°	362
60°	240
65°	155
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1174 cd/sqm



TEST NUMBER: P757019

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.9	40.5
10°-20°	166.3	39.9
20°-30°	54.3	13.0
30°-40°	18.5	4.4
40°-50°	6.2	1.5
50°-60°	1.9	0.4
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	389.4	93.5
0°-40°	407.9	97.9
0°-60°	416.0	99.8
0°-90°	416.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	416.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2372	
5°	2132	169
15°	590	166
25°	108	54
35°	28	18
45°	8	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P757019

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2371.6
0.5°	2371.6
1°	2368.7
1.5°	2362.8
2°	2352.0
2.5°	2337.6
3°	2317.3
3.5°	2289.1
4°	2247.0
4.5°	2195.9
5°	2131.5
5.5°	2046.8
6°	1960.0
6.5°	1860.6
7°	1763.2
7.5°	1649.2
8°	1547.4
8.5°	1444.9
9°	1350.3
9.5°	1263.5
10°	1182.6
12.5°	849.2
15°	589.6
17.5°	385.2
20°	242.9
22.5°	157.3
25°	108.1
27.5°	76.0
30°	54.7
32.5°	39.3
35°	27.9
37.5°	19.4
40°	13.9
42.5°	10.1
45°	7.6
47.5°	5.9
50°	4.0
52.5°	2.5
55°	1.9
57.5°	1.5
60°	1.1
62.5°	0.8
65°	0.6



TEST NUMBER: P757019

CATALOG NUMBER: LD6D02D010-EU6DR200210IC9040-6LBDP1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.4
70°		0.2

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)