

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843542

Luminaire Tested: **LD4C25DE010B2750 EU4C25B40 4LBNH**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P843542
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25DE010B2750 EU4C25B40 4LBNH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1560.1 lumens
Efficiency: N/A
Efficacy: 52.4 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843542

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P843542

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 | | | |
| 2 | 108 | 103 | 99 | 96 | 106 | 101 | 98 | 94 | 98 | 95 | 92 | 95 | 93 | 90 | 92 | 90 | 89 | 87 | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 95 | 90 | 86 | 92 | 88 | 85 | 90 | 86 | 84 | 87 | 85 | 82 | 81 | | | |
| 4 | 97 | 90 | 84 | 80 | 95 | 89 | 83 | 79 | 86 | 82 | 78 | 84 | 81 | 78 | 83 | 79 | 77 | 75 | | | |
| 5 | 92 | 84 | 78 | 74 | 91 | 83 | 78 | 73 | 81 | 76 | 73 | 80 | 75 | 72 | 78 | 74 | 72 | 70 | | | |
| 6 | 88 | 79 | 73 | 69 | 86 | 78 | 72 | 68 | 76 | 72 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 65 | | | |
| 7 | 83 | 74 | 68 | 64 | 82 | 73 | 68 | 64 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 63 | 61 | | | |
| 8 | 79 | 70 | 64 | 60 | 78 | 69 | 64 | 60 | 68 | 63 | 59 | 67 | 63 | 59 | 66 | 62 | 59 | 58 | | | |
| 9 | 76 | 66 | 60 | 56 | 74 | 65 | 60 | 56 | 65 | 59 | 56 | 64 | 59 | 56 | 63 | 59 | 55 | 54 | | | |
| 10 | 72 | 62 | 57 | 53 | 71 | 62 | 56 | 53 | 61 | 56 | 53 | 60 | 56 | 52 | 60 | 55 | 52 | 51 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 240621 |
| 5° | 235275 |
| 10° | 217537 |
| 15° | 195194 |
| 20° | 171829 |
| 25° | 147862 |
| 30° | 119076 |
| 35° | 79278 |
| 40° | 41232 |
| 45° | 18677 |
| 50° | 8104 |
| 55° | 5440 |
| 60° | 3489 |
| 65° | 2471 |
| 70° | 2047 |
| 75° | 1377 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P843542

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBNH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 176.7 | 11.3 |
| 10°-20° | 428.7 | 27.5 |
| 20°-30° | 497.7 | 31.9 |
| 30°-40° | 329.6 | 21.1 |
| 40°-50° | 92.4 | 5.9 |
| 50°-60° | 23.3 | 1.5 |
| 60°-70° | 8.7 | 0.6 |
| 70°-80° | 3.0 | 0.2 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1103.0 | 70.7 |
| 0°-40° | 1432.6 | 91.8 |
| 0°-60° | 1548.3 | 99.2 |
| 0°-90° | 1560.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1560.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1959 | |
| 5° | 1908 | 177 |
| 15° | 1535 | 429 |
| 25° | 1091 | 498 |
| 35° | 529 | 330 |
| 45° | 108 | 92 |
| 55° | 25 | 23 |
| 65° | 8 | 9 |
| 75° | 3 | 3 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P843542

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBNH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1958.6 |
| 2.5° | 1950.2 |
| 5° | 1907.8 |
| 7.5° | 1834.3 |
| 10° | 1743.8 |
| 12.5° | 1642.0 |
| 15° | 1534.7 |
| 17.5° | 1430.1 |
| 20° | 1314.3 |
| 22.5° | 1206.9 |
| 25° | 1090.8 |
| 27.5° | 980.7 |
| 30° | 839.4 |
| 32.5° | 689.6 |
| 35° | 528.6 |
| 37.5° | 378.7 |
| 40° | 257.1 |
| 42.5° | 166.7 |
| 45° | 107.5 |
| 47.5° | 65.0 |
| 50° | 42.4 |
| 52.5° | 31.1 |
| 55° | 25.4 |
| 57.5° | 19.9 |
| 60° | 14.2 |
| 62.5° | 11.3 |
| 65° | 8.5 |
| 67.5° | 5.7 |
| 70° | 5.7 |
| 72.5° | 2.9 |
| 75° | 2.9 |
| 77.5° | 2.9 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)