

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843546

Luminaire Tested: **LD4C25DE010B2750 EU4C25B40 4LBWH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25DE010B2750 EU4C25B40 4LBWH
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2087.8 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843546

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P843546

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82				82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61				61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55				55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50				50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46				46
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43				43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39				39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	165324
5°	165955
10°	166452
15°	166463
20°	165553
25°	161675
30°	151108
35°	130854
40°	102222
45°	73336
50°	47648
55°	28530
60°	16684
65°	10727
70°	7148
75°	5364
80°	4033
85°	0



TEST NUMBER: P843546

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.2	6.1
10°-20°	369.3	17.7
20°-30°	544.9	26.1
30°-40°	537.7	25.8
40°-50°	329.1	15.8
50°-60°	126.2	6.0
60°-70°	39.5	1.9
70°-80°	11.6	0.6
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1042.3	49.9
0°-40°	1580.0	75.7
0°-60°	2035.3	97.5
0°-90°	2087.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2087.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1346	
5°	1346	128
15°	1309	369
25°	1193	545
35°	872	538
45°	422	329
55°	133	126
65°	37	39
75°	11	12
85°	0	2
90°	0	



TEST NUMBER: P843546

CATALOG NUMBER: LD4C25DE010B2750 EU4C25B40 4LBWH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1345.7
2.5°	1348.5
5°	1345.7
7.5°	1342.9
10°	1334.3
12.5°	1323.0
15°	1308.8
17.5°	1291.8
20°	1266.3
22.5°	1238.1
25°	1192.7
27.5°	1136.0
30°	1065.2
32.5°	977.5
35°	872.5
37.5°	756.4
40°	637.4
42.5°	526.9
45°	422.1
47.5°	328.6
50°	249.3
52.5°	184.2
55°	133.2
57.5°	93.5
60°	67.9
62.5°	51.1
65°	36.9
67.5°	28.3
70°	19.9
72.5°	14.2
75°	11.3
77.5°	5.7
80°	5.7
82.5°	2.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)