

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843221

Luminaire Tested: **LD4C08DE010B2750 EU4C08B27 4LBNLI**

Issue Date: 2/16/2023



Test Information

Test Method: LM-79-08
Report Number: P843221
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 2/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08DE010B2750 EU4C08B27 4LBNLI
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 598.7 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843221

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B27 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P843221

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B27 4LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	189256
5°	170321
10°	132034
15°	95556
20°	66166
25°	48244
30°	35053
35°	20742
40°	8724
45°	2728
50°	344
55°	214
60°	246
65°	291
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P843221

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B27 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.4	20.3
10°-20°	207.8	34.7
20°-30°	165.2	27.6
30°-40°	87.4	14.6
40°-50°	15.1	2.5
50°-60°	1.2	0.2
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	494.4	82.6
0°-40°	581.9	97.2
0°-60°	598.1	99.9
0°-90°	598.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	598.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1540	
5°	1381	121
15°	751	208
25°	356	165
35°	138	87
45°	16	15
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P843221

CATALOG NUMBER: LD4C08DE010B2750 EU4C08B27 4LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1540.5
2.5°	1500.9
5°	1381.1
7.5°	1224.3
10°	1058.4
12.5°	897.9
15°	751.3
17.5°	614.9
20°	506.1
22.5°	423.2
25°	355.9
27.5°	301.4
30°	247.1
32.5°	191.7
35°	138.3
37.5°	91.3
40°	54.4
42.5°	31.3
45°	15.7
47.5°	5.5
50°	1.8
52.5°	1.8
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)