

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762867

Luminaire Tested: LD6D25D010-EU6DR1515309024-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P762867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR1515309024-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2630.0 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P762867
CATALOG NUMBER: LD6D25D010-EU6DR1515309024-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P762867

CATALOG NUMBER: LD6D25D010-EU6DR1515309024-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4031837	4031837	4031837
5°	2369295	2338613	2357120
10°	707122	712077	722975
15°	175894	179316	173783
20°	52628	60942	53741
25°	18556	23635	18790
30°	6814	8971	6927
35°	3413	3856	3304
40°	2152	2372	2152
45°	1596	1701	1596
50°	1266	1266	1266
55°	1058	1058	1058
60°	850	850	850
65°	649	649	649
70°	556	556	556
75°	348	348	461
80°	236	236	236
85°	125	125	125

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1701 cd/sqm



TEST NUMBER: P762867

CATALOG NUMBER: LD6D25D010-EU6DR1515309024-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1705.7	64.9
10°-20°	701.6	26.7
20°-30°	139.4	5.3
30°-40°	34.8	1.3
40°-50°	18.3	0.7
50°-60°	13.6	0.5
60°-70°	9.6	0.4
70°-80°	5.5	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2546.6	96.8
0°-40°	2581.4	98.2
0°-60°	2613.3	99.4
0°-90°	2630.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2630.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	35832	35832	35832	35832	35832	
5°	23313	23074	23011	23171	23193	1702
15°	2025	2063	2064	2028	2001	694
25°	238	270	303	268	241	125
35°	47	50	53	50	46	32
45°	23	23	24	23	23	18
55°	15	15	15	15	15	14
65°	9	9	9	9	9	10
75°	5	5	5	5	6	5
85°	2	2	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P762867

CATALOG NUMBER: LD6D25D010-EU6DR1515309024-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	35832.2	35832.2	35832.2	35832.2	35832.2
2.5°	32322.1	32349.4	32360.0	32391.8	32510.2
5°	23313.2	23073.5	23011.3	23170.6	23193.4
7.5°	13809.8	13858.4	14035.9	14075.3	13932.7
10°	7578.4	7640.6	7631.5	7686.1	7748.3
12.5°	3875.7	3827.1	3812.0	3874.2	3787.7
15°	2025.1	2063.0	2064.5	2028.1	2000.8
17.5°	1089.1	1133.1	1205.9	1146.8	1055.8
20°	643.2	682.6	744.8	696.3	656.8
22.5°	397.4	429.3	473.3	435.3	403.5
25°	238.2	270.0	303.4	268.5	241.2
27.5°	141.1	168.4	189.6	166.9	139.6
30°	91.0	106.2	119.8	104.7	92.5
32.5°	63.7	69.8	75.8	69.8	63.7
35°	47.0	50.1	53.1	50.1	45.5
37.5°	36.4	39.4	41.0	37.9	34.9
40°	30.3	31.9	33.4	31.9	30.3
42.5°	25.8	27.3	27.3	27.3	25.8
45°	22.8	22.8	24.3	22.8	22.8
47.5°	19.7	19.7	21.2	19.7	19.7
50°	18.2	18.2	18.2	18.2	18.2
52.5°	16.7	16.7	16.7	16.7	16.7
55°	15.2	15.2	15.2	15.2	15.2
57.5°	13.7	13.7	13.7	13.7	13.7
60°	12.1	12.1	12.1	12.1	12.1
62.5°	10.6	10.6	10.6	10.6	10.6
65°	9.1	9.1	9.1	9.1	9.1
67.5°	9.1	9.1	9.1	9.1	9.1
70°	7.6	7.6	7.6	7.6	7.6
72.5°	6.1	6.1	6.1	6.1	6.1
75°	4.6	4.6	4.6	4.6	4.6
77.5°	4.6	4.6	4.6	4.6	4.6
80°	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	3.0	3.0	3.0	3.0
85°	1.5	1.5	1.5	1.5	1.5
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)