

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P762985

Luminaire Tested: LD6D25D010-EU6DR2015309035-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P762985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR2015309035-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3506.0 lumens
Efficiency: N/A
Efficacy: 139.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P762985
CATALOG NUMBER: LD6D25D010-EU6DR2015309035-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P762985

CATALOG NUMBER: LD6D25D010-EU6DR2015309035-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	100	99	98	98	96	95	94													
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	98	96	95	98	96	95	94													
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	98	96	95	98	96	95	94													
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	93	91	89	93	91	89	88													
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	91	88	86	91	88	86	85													
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	88	86	84	88	86	84	83													
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	86	84	82	86	84	82	81													
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	84	82	80	84	82	80	79													
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	82	80	78	82	80	78	77													
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	81	78	76	81	78	76	75													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2180287
5°	1967033
10°	1104004
15°	561186
20°	237604
25°	109682
30°	58060
35°	31292
40°	16730
45°	9889
50°	5745
55°	3048
60°	1945
65°	1370
70°	575
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9889 cd/sqm



TEST NUMBER: P762985

CATALOG NUMBER: LD6D25D010-EU6DR2015309035-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1420.8	40.5
10°-20°	1399.0	39.9
20°-30°	457.0	13.0
30°-40°	155.6	4.4
40°-50°	52.3	1.5
50°-60°	15.7	0.4
60°-70°	5.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3276.8	93.5
0°-40°	3432.4	97.9
0°-60°	3500.5	99.8
0°-90°	3506.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3506.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19955	
5°	17935	###
15°	4961	1399
25°	910	457
35°	235	156
45°	64	52
55°	16	16
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P762985

CATALOG NUMBER: LD6D25D010-EU6DR2015309035-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	19954.9
0.5°	19954.9
1°	19930.1
1.5°	19880.3
2°	19789.7
2.5°	19668.9
3°	19498.3
3.5°	19260.2
4°	18906.6
4.5°	18476.5
5°	17934.6
5.5°	17222.0
6°	16491.7
6.5°	15654.8
7°	14835.6
7.5°	13876.1
8°	13019.6
8.5°	12157.8
9°	11361.7
9.5°	10631.4
10°	9950.8
12.5°	7145.0
15°	4961.2
17.5°	3241.1
20°	2043.5
22.5°	1323.8
25°	909.8
27.5°	639.7
30°	460.2
32.5°	330.5
35°	234.6
37.5°	163.5
40°	117.3
42.5°	85.3
45°	64.0
47.5°	49.8
50°	33.8
52.5°	21.3
55°	16.0
57.5°	12.4
60°	8.9
62.5°	7.1
65°	5.3



TEST NUMBER: P762985
CATALOG NUMBER: LD6D25D010-EU6DR2015309035-6LBS1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		3.6
70°		1.8

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)