

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763011

Luminaire Tested: LD6D25D010-EU6DR2015309050-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR2015309050-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3560.4 lumens
Efficiency: N/A
Efficacy: 141.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763011
CATALOG NUMBER: LD6D25D010-EU6DR2015309050-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P763011
 CATALOG NUMBER: LD6D25D010-EU6DR2015309050-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94															
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	98	96	95	94															
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	95	93	92	91															
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	93	91	89	88															
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	91	88	86	85															
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	88	86	84	83															
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	86	84	82	81															
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	84	82	80	79															
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	82	80	78	77															
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	81	78	76	75															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2214158
5°	1997578
10°	1121157
15°	569896
20°	241289
25°	111382
30°	58969
35°	31772
40°	16987
45°	10044
50°	5830
55°	3086
60°	1967
65°	1396
70°	575
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10044 cd/sqm



TEST NUMBER: P763011

CATALOG NUMBER: LD6D25D010-EU6DR2015309050-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1442.8	40.5
10°-20°	1420.7	39.9
20°-30°	464.1	13.0
30°-40°	158.0	4.4
40°-50°	53.1	1.5
50°-60°	16.0	0.4
60°-70°	5.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3327.7	93.5
0°-40°	3485.7	97.9
0°-60°	3554.8	99.8
0°-90°	3560.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3560.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20265	
5°	18213	###
15°	5038	1421
25°	924	464
35°	238	158
45°	65	53
55°	16	16
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P763011
CATALOG NUMBER: LD6D25D010-EU6DR2015309050-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	20264.9
0.5°	20264.9
1°	20239.6
1.5°	20189.1
2°	20097.1
2.5°	19974.3
3°	19801.1
3.5°	19559.3
4°	19200.2
4.5°	18763.5
5°	18213.1
5.5°	17489.5
6°	16747.8
6.5°	15897.9
7°	15066.0
7.5°	14091.6
8°	13221.8
8.5°	12346.6
9°	11538.2
9.5°	10796.5
10°	10105.4
12.5°	7256.0
15°	5038.2
17.5°	3291.5
20°	2075.2
22.5°	1344.4
25°	923.9
27.5°	649.6
30°	467.4
32.5°	335.6
35°	238.2
37.5°	166.0
40°	119.1
42.5°	86.6
45°	65.0
47.5°	50.5
50°	34.3
52.5°	21.7
55°	16.2
57.5°	12.6
60°	9.0
62.5°	7.2
65°	5.4



TEST NUMBER: P763011
CATALOG NUMBER: LD6D25D010-EU6DR2015309050-6LBS1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		3.6
70°		1.8

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)