

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843451

Luminaire Tested: **LD4C20DE010B35 EU4C20B35 4LBCSMMS**

Issue Date: 5/7/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P843451  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C20DE010B35 EU4C20B35 4LBCSMMS  
Description: 4in Downlight with BioUp LEDs  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1355.9 lumens  
Efficiency: N/A  
Efficacy: 62.2 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843451

CATALOG NUMBER: LD4C20DE010B35 EU4C20B35 4LBCSMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P843451

CATALOG NUMBER: LD4C20DE010B35 EU4C20B35 4LBCSMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	68036
5°	67988
10°	67963
15°	67308
20°	66833
25°	66164
30°	65042
35°	63950
40°	62065
45°	59958
50°	56401
55°	51020
60°	44817
65°	37732
70°	29490
75°	20648
80°	11674
85°	8035



TEST NUMBER: P843451

CATALOG NUMBER: LD4C20DE010B35 EU4C20B35 4LBCSMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.5	3.9
10°-20°	149.4	11.0
20°-30°	224.7	16.6
30°-40°	266.3	19.6
40°-50°	265.0	19.5
50°-60°	213.7	15.8
60°-70°	129.2	9.5
70°-80°	48.0	3.5
80°-90°	7.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	426.6	31.5
0°-40°	692.9	51.1
0°-60°	1171.6	86.4
0°-90°	1355.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1355.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	554	
5°	551	52
15°	529	149
25°	488	225
35°	426	266
45°	345	265
55°	238	214
65°	130	129
75°	44	48
85°	6	7
90°	0	



TEST NUMBER: P843451

CATALOG NUMBER: LD4C20DE010B35 EU4C20B35 4LBCSMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	553.8
2.5°	553.8
5°	551.3
7.5°	549.7
10°	544.8
12.5°	536.5
15°	529.2
17.5°	521.0
20°	511.2
22.5°	501.2
25°	488.1
27.5°	474.0
30°	458.5
32.5°	443.7
35°	426.4
37.5°	408.4
40°	387.0
42.5°	366.5
45°	345.1
47.5°	321.2
50°	295.1
52.5°	267.8
55°	238.2
57.5°	212.1
60°	182.4
62.5°	156.1
65°	129.8
67.5°	105.1
70°	82.1
72.5°	61.7
75°	43.5
77.5°	27.9
80°	16.5
82.5°	9.8
85°	5.7
87.5°	2.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)