

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766998

Luminaire Tested: LD6D45BD010-EU6DR7040509024-6LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P766998  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D45BD010-EU6DR7040509024-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4453.6 lumens  
Efficiency: N/A  
Efficacy: 115.1 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P766998

CATALOG NUMBER: LD6D45BD010-EU6DR7040509024-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P766998

CATALOG NUMBER: LD6D45BD010-EU6DR7040509024-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	547080
5°	530820
10°	516033
15°	509255
20°	475544
25°	357255
30°	252541
35°	89460
40°	47039
45°	50095
50°	51878
55°	52861
60°	53188
65°	52069
70°	49132
75°	45508
80°	40395
85°	32845

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 53197 cd/sqm



TEST NUMBER: P766998

CATALOG NUMBER: LD6D45BD010-EU6DR7040509024-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	456.5	10.3
10°-20°	1252.2	28.1
20°-30°	1379.1	31.0
30°-40°	526.9	11.8
40°-50°	248.8	5.6
50°-60°	247.3	5.6
60°-70°	198.1	4.4
70°-80°	113.8	2.6
80°-90°	31.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3087.8	69.3
0°-40°	3614.7	81.2
0°-60°	4110.8	92.3
0°-90°	4453.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4453.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5007	
5°	4840	456
15°	4502	1252
25°	2963	1379
35°	671	527
45°	324	249
55°	278	247
65°	201	198
75°	108	114
85°	26	31
90°	0	



TEST NUMBER: P766998

CATALOG NUMBER: LD6D45BD010-EU6DR7040509024-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5007.1
2.5°	4954.8
5°	4839.8
7.5°	4743.9
10°	4651.2
12.5°	4572.7
15°	4502.1
17.5°	4331.7
20°	4089.9
22.5°	3568.2
25°	2963.4
27.5°	2579.7
30°	2001.7
32.5°	1293.0
35°	670.7
37.5°	362.3
40°	329.8
42.5°	327.4
45°	324.2
47.5°	317.1
50°	305.2
52.5°	291.7
55°	277.5
57.5°	261.6
60°	243.4
62.5°	222.8
65°	201.4
67.5°	177.6
70°	153.8
72.5°	130.0
75°	107.8
77.5°	84.8
80°	64.2
82.5°	45.2
85°	26.2
87.5°	10.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)