

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843486

Luminaire Tested: **LD4C20DE010B50 EU4C20B50 4LBNH**

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P843486  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C20DE010B50 EU4C20B50 4LBNH  
Description: 4in Downlight with BioUp LEDs  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1269.2 lumens  
Efficiency: N/A  
Efficacy: 58.2 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.8  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P843486

CATALOG NUMBER: LD4C20DE010B50 EU4C20B50 4LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P843486

CATALOG NUMBER: LD4C20DE010B50 EU4C20B50 4LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	76	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	195767
5°	191409
10°	176981
15°	158793
20°	139798
25°	120304
30°	96875
35°	64490
40°	33550
45°	15185
50°	6594
55°	4412
60°	2826
65°	2006
70°	1688
75°	1092
80°	0
85°	0



TEST NUMBER: P843486

CATALOG NUMBER: LD4C20DE010B50 EU4C20B50 4LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.8	11.3
10°-20°	348.7	27.5
20°-30°	404.9	31.9
30°-40°	268.1	21.1
40°-50°	75.2	5.9
50°-60°	18.9	1.5
60°-70°	7.1	0.6
70°-80°	2.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	897.4	70.7
0°-40°	1165.5	91.8
0°-60°	1259.6	99.2
0°-90°	1269.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1269.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1594	
5°	1552	144
15°	1248	349
25°	888	405
35°	430	268
45°	87	75
55°	21	19
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P843486

CATALOG NUMBER: LD4C20DE010B50 EU4C20B50 4LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1593.5
2.5°	1586.6
5°	1552.1
7.5°	1492.2
10°	1418.7
12.5°	1335.9
15°	1248.5
17.5°	1163.5
20°	1069.3
22.5°	981.8
25°	887.5
27.5°	797.9
30°	682.9
32.5°	561.1
35°	430.0
37.5°	308.1
40°	209.2
42.5°	135.6
45°	87.4
47.5°	52.9
50°	34.5
52.5°	25.3
55°	20.6
57.5°	16.2
60°	11.5
62.5°	9.2
65°	6.9
67.5°	4.7
70°	4.7
72.5°	2.3
75°	2.3
77.5°	2.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)