

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843521

Luminaire Tested: **LD4C25DE010B35 EU4C25B35 4LBCSMMS**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P843521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206301)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25DE010B35 EU4C25B35 4LBCSMMS
Description: 4in Downlight with BioUp LEDs
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1780.0 lumens
Efficiency: N/A
Efficacy: 59.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 29.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843521

CATALOG NUMBER: LD4C25DE010B35 EU4C25B35 4LBCSMMS

Luminous Intensity Polar Plot





TEST NUMBER: P843521

CATALOG NUMBER: LD4C25DE010B35 EU4C25B35 4LBCSMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89302
5°	89261
10°	89220
15°	88370
20°	87725
25°	86849
30°	85385
35°	83972
40°	81486
45°	78722
50°	74023
55°	66977
60°	58822
65°	49535
70°	38722
75°	27104
80°	15282
85°	10572



TEST NUMBER: P843521

CATALOG NUMBER: LD4C25DE010B35 EU4C25B35 4LBCSMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.9	3.9
10°-20°	196.1	11.0
20°-30°	295.0	16.6
30°-40°	349.6	19.6
40°-50°	347.9	19.5
50°-60°	280.5	15.8
60°-70°	169.6	9.5
70°-80°	63.0	3.5
80°-90°	9.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	560.0	31.5
0°-40°	909.6	51.1
0°-60°	1538.0	86.4
0°-90°	1780.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1780.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	727	
5°	724	69
15°	695	196
25°	641	295
35°	560	350
45°	453	348
55°	313	280
65°	170	170
75°	57	63
85°	8	9
90°	0	



TEST NUMBER: P843521

CATALOG NUMBER: LD4C25DE010B35 EU4C25B35 4LBCSMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	726.9
2.5°	726.9
5°	723.8
7.5°	721.6
10°	715.2
12.5°	704.4
15°	694.8
17.5°	684.0
20°	671.0
22.5°	658.1
25°	640.7
27.5°	622.3
30°	601.9
32.5°	582.4
35°	559.9
37.5°	536.1
40°	508.1
42.5°	481.1
45°	453.1
47.5°	421.7
50°	387.3
52.5°	351.6
55°	312.7
57.5°	278.4
60°	239.4
62.5°	205.0
65°	170.4
67.5°	138.0
70°	107.8
72.5°	80.9
75°	57.1
77.5°	36.7
80°	21.6
82.5°	12.9
85°	7.5
87.5°	3.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)