

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767010

Luminaire Tested: LD6D45BD010-EU6DR7040509027-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P767010
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR7040509027-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4804.7 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P767010
CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P767010

CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	590216
5°	572673
10°	556706
15°	549411
20°	513031
25°	385417
30°	272450
35°	96516
40°	50748
45°	54050
50°	55974
55°	57014
60°	57384
65°	56153
70°	52998
75°	49096
80°	43604
85°	35352

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 57386 cd/sqm



TEST NUMBER: P767010

CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	492.5	10.3
10°-20°	1350.9	28.1
20°-30°	1487.8	31.0
30°-40°	568.5	11.8
40°-50°	268.4	5.6
50°-60°	266.8	5.6
60°-70°	213.6	4.4
70°-80°	122.8	2.6
80°-90°	33.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3331.2	69.3
0°-40°	3899.6	81.2
0°-60°	4434.9	92.3
0°-90°	4804.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4804.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5402	
5°	5221	492
15°	4857	1351
25°	3197	1488
35°	724	568
45°	350	268
55°	299	267
65°	217	214
75°	116	123
85°	28	33
90°	0	



TEST NUMBER: P767010

CATALOG NUMBER: LD6D45BD010-EU6DR7040509027-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5401.9
2.5°	5345.4
5°	5221.4
7.5°	5117.9
10°	5017.8
12.5°	4933.2
15°	4857.1
17.5°	4673.2
20°	4412.3
22.5°	3849.6
25°	3197.0
27.5°	2783.0
30°	2159.5
32.5°	1394.9
35°	723.6
37.5°	390.9
40°	355.8
42.5°	353.2
45°	349.8
47.5°	342.1
50°	329.3
52.5°	314.7
55°	299.3
57.5°	282.2
60°	262.6
62.5°	240.3
65°	217.2
67.5°	191.6
70°	165.9
72.5°	140.3
75°	116.3
77.5°	91.5
80°	69.3
82.5°	48.8
85°	28.2
87.5°	11.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)